



8 ANHÄNGER ANKOPPELN / COUPLE THE TRAILER / L'ATTELAGE DES REMORQUES / AANHANGWAGENS AANKOPPELEN / ENGANCHE DE REMOLQUES / AGGANCIARE I RIMORCHI / AGGANCIARE I RIMORCHI / KOBLE TILHENGEREN / OPSPÆNDING AF TRAILERE



8A
Zapfen des Trailers von oben in die LKW-Kupplung stecken / Insert the trailer's pin into the truck coupling from above / Insérez l'embout de la remorque dans l'attelage du camion par le haut / Steek de spigot van de aanhanger van bovenaf in de koppeling van de vrachtwagen / Introduzca la espiga del remolque en el acoplamiento del camión desde arriba / Inserire il raccordo del rimorchio nel gancio di traino dall'alto / Sätt in släpvagnens spigg i lastbilens koppling upifrån / Sett pinnen på tilhengeren inn i lastebil-koblingen ovenfra / Sæt anhængerens spigot ind i lastbilens kobling fra oven

9 TRAILER-STÜTZEN EIN- UND AUSFAHREN / RETRACT AND EXTEND TRAILER SUPPORTS / SUPPORTS DE REMORQUE EXTENSIBLES ET RÉTRACTABLES / UITSCHUIVEN EN INTREKKEN VAN TRAILERSTEUNEN / SOPORTES DE REMOLQUE EXTENSIBLES Y RETRÁCTILES / ESTENSIONE E RITRAZIONE DEI SUPPORTI DEL RIMORCHIO / FÖRLÄNGNING OCH INDRAGNING AV SLÄPVAGNSSTÖDEN / TREKK UT TILHENGERSTÖTTENE OG TREKK DEM INN / UD- OG INDTRÆK AF ANHÆNGERSTØTTER



Trailer-Stützen ausfahren / Extend trailer supports / Prolonger les supports de la remorque / Aanhangwagensteunen verlengen / Extender los soportes del remolque / Estendere i supporti del rimorchio / Utöka stöd för släpvagnar / Forlæng tilhengerstøttene / Forlængelse af anhængerstøt-ter



Trailer-Stützen einfahren / Retract trailer supports / Rétracter les supports de la remorque / Aanhangwagensteunen intrekken / Retirar los soportes del remolque / Ritirare i supporti del rimorchio / Dra in släpvagnsstöden / Trekk inn tilhengerstøttene / Træk trailerstøtterne tilbage

10 INHALT / TABLE OF CONTENTS / CONTENU / INHOUD / CONTENIDO / CONTENUTO / INNEHÅLL / INNHold / INDHOLD



SERVICE?



SCAN ME

(only DE, GB, FR)
www.revell-service.de

"Mercedes-Benz", ,  and the design of the enclosed product are subject to intellectual property protection owned by Daimler AG. They are used by Shantou Chenghai Qingyitoy LTD under license.

Licensee: Shantou Chenghai Qingyitoy LTD
Manufacture: Shantou Chenghai Qingyitoy LTD
Manufacture address: Xinanin Industrial Area,
Chenghai, Guangdong, China
Made in China

24534

8+

Revell
Control

RC SHOW TRUCK
MERCEDES-BENZ ACTROS
DINO EXPRESS



USER MANUAL

DE GB FR NL ES IT SE NO DK



Revell


www.revell-control.de

© 2021 Revell GmbH, Henschelstr. 20-30, D-32257 Bünde.
REVELL IS THE REGISTERED TRADEMARK OF REVELL GMBH, GERMANY. Made in China.


Distributed in the UK by: Carrera Revell UK LTD, Unit 10, Old Airfield Industrial Estate,
Cheddington Lane, Tring HP23 4QR, United Kingdom

V 01.0

1 ÜBERSICHT DES MODELLS / OVERVIEW OF THE MODEL / APERÇU DU MODÈLE / OVERZICHT VAN HET MODEL / PANORAMICA GENERALE DEL MODELLO / ÖVERSIKT ÖVER MODELLEN / VISTA GENERAL DEL MODELO / ÖVERSIKT OVER MODELLEN / OVERSIGT OVER MODELLERNE



2 ÜBERSICHT DER FERNSTEUERUNG / OVERVIEW OF THE REMOTE CONTROL / APERÇU DE LA TÉLÉCOMMANDE / OVERZICHT VAN DE AFSTANDBEDIENING / PANORAMICA GENERALE DEL RADIOCOMANDO / ÖVERSIKT ÖVER FJÄRRKONTROLLEN / VISTA GENERAL DEL CONTROL REMOTO / ÖVERSIKT FJERNKONTROLL / ÖVERSIKT OVER FJERNBETJENING



3 FERNSTEUERUNG / REMOTE CONTROL / TÉLÉCOMMANDE / AFSTANDBESTURING / CONTROL REMOTO / TELECOMANDO / FJÄRRKONTROLL / FJERNSTYRING / FJERNSTYRING



DE Batterien/Akkus für die Fernsteuerung:
Stromversorgung: DC 3,0 V == Batterien: 2 x 1,5 V „AA“ (nicht mitgeliefert)

GB Batteries/rechargeable batteries for the remote control:
Power supply: DC 3.0 V == Batteries: 2 x 1.5 V "AA" (not included)

FR Batteries / accus pour la télécommande :
Alimentation : Batteries 3.0 V D.C. == : 2 x 1,5 V « AA » (non fournies)

NL Batterijen/accu's voor de afstandsbesturing:
Stroomvoorziening: DC 3.0 V == Batterijen: 2 x 1.5 V "AA" (niet meegeleverd)

ES Pilas/baterías para el control remoto:
Suministro de corriente: DC 3.0 V == Pilas: 2 x 1.5 V "AA"

DE Frequenzbereich: 2400 - 2483,5 MHz
Maximale Sendeleistung: < 10 dBm

GB Frequency range: 2400 - 2483.5 MHz
Maximum transmitter power: < 10 dBm

FR Bande de fréquence : 2400 - 2483,5 MHz
Puissance maximale de l'émetteur : < 10 dBm

NL Frequentiegebied: 2400 - 2483,5 MHz
Maximaal zendvermogen: < 10 dBm

ES Rango de frecuencia: 2400 - 2483,5 MHz

DE Batterien/Akkus für das Modell:
Stromversorgung: == DC 6,0 V Batterie: 4 x 1,5 V „AA“ (nicht mitgeliefert)

GB Batteries/rechargeable batteries for the model:
Power supply: DC 6,0 V == Batteries: 4 x 1,5 V "AA" (not included)

FR Batteries/accus du dèle :
Alimentation : DC 6,0 V == Piles : 4 x 1,5 V «AA» (non fournies)

NL Batterijen/accu's voor het model:
Voeding: DC 6,0 V == Batterijen: 4 x 1,5 V "AA" (niet meegeleverd)

ES Pilas/baterías para el modelo:
Alimentación: DC 6,0 V == Baterías: 4 x 1,5 V "AA" (no incluidas)


IT Batterie/batterie ricaricabili per il telecomando:
Alimentazione elettrica: DC 3.0 V == Batterie: 2 x 1.5 V "AA" (non fornite)

SE Batterier/uppladdningsbarabatterier till fjärrkontrollen:
Strömförsörjning: DC 3,0 V == Batterier: 2 x 1,5 V "AA" (medföljer ej)

NO Batterier / oppladbare batterier til fjernstyringen:
Strømforsyning: DC 3.0 V == Batterier: 2 x 1.5 V "AA" (medfølger ikke)

DK Batterier/oplader til fjernstyringen:
Strømforsyning: DC 3.0 V == Batterier: 2 x 1.5 V "AA" (medfølger ikke)

4 BATTERIE-FACH/ BATTERY COMPARTMENT / COMPARTIMENT DES PILES / BATTERIJVAK / COMPARTIMENTO DE LA BATERIA / COMPARTIMENTO DELLA BATTERIA / BATTERIFACK / BATTERIROM / BATTERIROM



(no suministradas)

IT Batterie/batterie ricaricabili per il telecomando:
Alimentazione elettrica: DC 3.0 V == Batterie: 2 x 1.5 V "AA" (non fornite)

SE Batterier/uppladdningsbarabatterier till fjärrkontrollen:
Strömförsörjning: DC 3,0 V == Batterier: 2 x 1,5 V "AA" (medföljer ej)

NO Batterier / oppladbare batterier til fjernstyringen:
Strømforsyning: DC 3.0 V == Batterier: 2 x 1.5 V "AA" (medfølger ikke)

DK Batterier/oplader til fjernstyringen:
Strømforsyning: DC 3.0 V == Batterier: 2 x 1.5 V "AA" (medfølger ikke)

Potencia máxima del transmisor: < 10 dBm

IT Intervallo di frequenza: 2400 - 2483,5 MHz
Potenza massima del trasmettitore: < 10 dBm

SE Frekvensområde: 2 400 - 2 483,5 MHz
Maximal sändareffekt: < 10 dBm

NO Frekvensområde: 2400 - 2483,5 MHz
Maksimal sendereffekt: < 10 dBm

DK Frekvensområde: 2400 - 2483,5 MHz
Maksimal sendereffekt: < 10 dBm


L Batterie/batterie ricaricabili per il modello:
Alimentazione: DC 6,0 V == Batterie: 4 x 1,5 V "AA" (non fornite)

SE Batterier/uppladdnings bara batterier till modellen:
Strömförsörjning: DC 6,0 V == Batterier: 4 x 1,5 V "AA" (medföljer inte)


NO Batterier/for modellen:
Strømforsyning: DC 6,0 V == batterier: 4 x 1,5 V "AA" (følger ikke med)

DK Batterier/til modellflyet:
Strømforsyning: DC 6,0 V == Batterier: 4 x 1,5 V "AA" (medfølger ikke)

5 STARTEN DES MODELLS / STARTING THE MODEL / DÉMARRER LE MODÈLE / STARTEN VAN HET MODEL / AVVIARE IL MODELLO / STARTA MODELLEN / DESPEGUE DEL MODELO / STARTE MODELLEN / START AF MODELLEN



6 TRIMMUNG / TRIMMING / TRIM / TRIMMEN / RECORTE / TRIM / TRIM / LISTVERK / TRIMME



7 FAHRZEUGSTEUERUNG / VEHICLE CONTROL / CONTRÔLE DU VÉHICULE / BESTUREN VAN DE AUTO / CONTROL DEL VEHICULO / COMANDO DEL VEICOLO / STYRA BILEN / BILSTYRING / KØRETØJSSTYRING

