



1200 watt max.

Soft touch housing

Hanging loop

Without decoration

**Hair dryer**  
HTD 3429

- Compact travelling hair dryer
- Folding handle
- 2 temperature/power settings
- Shaping nozzle 360° rotatable (removable)
- Soft touch housing
- Incl. volume diffuser
- Incl. see-through bag for practical storage and when travelling
- Switchable voltage: 110/230 V
- Hanging loop
- 110/230 V, 50/60 Hz, 1100–1200 W



Space-saving due to folding handle

Colour: Red  
Article no.: 264 558  
Article EAN-Code: 4 006 160 645 583  
Exportpack EAN-Code: 4 006 160 539 776

Colour: Blue  
Article no.: 263 558  
Article EAN-Code: 4 006 160 635 584  
Exportpack EAN-Code: 4 006 160 539 769

PU: 12  
20"/40"/HQ container: 8640 / 17280 / 20976

Dimensions: (approx. W x H x D)  
Unit: 170 x 235 x 75 mm  
Box: 220 x 155 x 80 mm