

2 temperature/  
power settings

Cold setting for  
style fix

800 watt



1 volume styler  
(Ø approx. 35 mm)

1 volume styler  
(Ø approx. 25 mm)

## PC-HAS 3011 Hot air styler

Without decoration

- > Hot air styler for even and gentle heat distribution
- > 2 exchangeable brush attachments with smooth bristles for hair gentle styling:
  - 1 volume styler with coarse bristles (Ø approx. 25 mm)
  - 1 volume styler with smooth bristles (Ø approx. 35 mm)
- > 2 temperature/power settings
- > Cold setting for style fix and hairstyle finish
- > Ergonomically shaped handle
- > Cable attached via 360° turnable joint
- > Overheating protection
- > Hanging loop
- > 220–240 V, 50/60 Hz, 800 W



Product:	Art.no.:	20"/40"/HQ-Container:
PC-HAS 3011	330 110	7740 / 15480 / 18822
Colour: White/	Art.EAN:	Device (W x H x D):
Champagner	4 006 160 301 106	260 x 60 x 60 mm; 0,3 kg
PU:	Export carton EAN:	Packaging (W x H x D):
6	4 006 160 038 903	410 x 110 x 65 mm;
Delivery:		

Product:	Art.no.:	20"/40"/HQ-Container:
PC-HAS 3011	330 111	7740 / 15480 / 18822
Colour:	Art.EAN:	Device (W x H x D):
Brown-bronze	4 006 160 301 113	260 x 60 x 60 mm; 0,3 kg
PU:	Export carton EAN:	Packaging (W x H x D):
6	4 006 160 038 910	410 x 110 x 65 mm;
Delivery:		

