

1400 watt

2 temperature/
power settings

Cold setting
for style fix



PC-HT 3009 Hairdryer

- > Compact hair dryer with 1400 watt
- > Folding handle
- > 2 temperature/power settings
- > Removable shaped nozzle, rotatable through 360°
- > Cold setting for style fix and hairstyle finish
- > Overheating protection
- > Hanging loop
- > 220–240 V, 50/60 Hz, 1400 W

Without decoration



Space-saving storage with
folding handle

Fitting accessories
(not included):

PC-HAS 3011
Hot air styler

Art. no.: 330 110 (White/champagne)
Art. no.: 330 111 (Brown/bronze)



Product:	Art.no.:	20"/40"/HQ-Container:
PC-HT 3009	330 090	6774 / 13554 / 16458
Colour: White/	Art.EAN:	Device (W x H x D):
Champagner	4 006 160 300 901	160 x 250 x 70 mm; 0,3 kg
PU:	Export carton EAN:	Packaging (W x H x D):
6	4 006 160 038 880	170 x 250 x 80 mm
Delivery:		

Product:	Art.no.:	20"/40"/HQ-Container:
PC-HT 3009	330 091	6774 / 13554 / 16458
Colour:	Art.EAN:	Device (W x H x D):
Brown-Bronze	4 006 160 300 918	160 x 250 x 70 mm; 0,3 kg
PU:	Export carton EAN:	Packaging (W x H x D):
6	4 006 160 038 897	170 x 250 x 80 mm
Delivery:		

