



Stainless steel housing

Food dryer for drying fruit, vegetables, herbs, meat etc. Rich in essential minerals for well-being, fitness and health.



PC-DR 1116 Food dryer

- > Food dryer for drying fruit, vegetables, herbs, meat etc. Rich in essential minerals for well-being, fitness and health
- > 7-step, electronic temperature setting (40–70 °C)
- > Electronic temperature display (switchable °C / °F)
- > Electronic timer (1–48 hours) with time remaining indicator
- > LCD display
- > Variable use due to 4 large (32 x 25 cm), transparent and stackable levels (easy cleaning) for up to 2 kg of food to be dried*)
- > Circulation fan, air circulation function
- > Overheating protection
- > Non-slip stand due to rubberized feet
- > 230 V, 50/60 Hz, 350 W

*) For processing/drying foods that contain large amounts of water such as apples, pineapple etc.

Without decoration



Variable use due to 4 large and stackable levels



LCD display (temperature and time remaining indicator)

| | | |
|-----------------|--------------------|---------------------------|
| Product: | Art. no: | 20" / 40" / HQ-Container: |
| PC-DR 1116 | 501 116 | 798 / 1634 / 1852 |
| Colour: Black / | Art. EAN: | Device (W x H x D): |
| Stainless steel | 4 006 160 501 117 | 340 x 260 x 260 mm |
| PU: | Export carton EAN: | Packaging (W x H x D): |
| 2 | 4 006 160 874 365 | 373 x 293 x 300 mm |