

Datenblatt

Art Nr.	20178
Model	PB20
Name	Powerbank Tank Plus 20000mAh / 18W
EAN Code	8717809201782

**Beschreibung**

Pro User Powerbank 20.000mAh: Pro User Powerbank 20000mAh:
Moderner Kraftprotz mit USB-C Power Delivery PD
18W Fast Charge

2 Ausgängen und Durchgangs-Ladefunktion

Garantie: 12 Monate
Umverpackungsmaße (20,5 x 10 x 4 cm)

Produktspezifikationen

Size: approx. 172*61*22mm

Color: Black

Charging cable: Length approx. 300mm, Micro USB to USB cable

Material: Aluminum alloy + PC + ABS

Input 1 (Micro USB): 5V = 2A, 9V = 2A, 12V = 1.5A

Input 2 (Type-C PD 3.0): 5V = 2.4A, 9V = 2A, 12V = 1.5A

Output 1 (Type-C PD 3.0): 5V = 2.4A, 9V = 2A, 12V = 1.5A

Output 2 (USB QC 3.0): 5V ~ 6.5V = 3A, 6.5V ~ 9V = 2A, 9V ~ 12V = 1.5A

Max. Output Power: 18W

Capacity: approx. 20,000mAh

Working temperature: 0°C to 40°C

Electrical Safeguards: Protection against: overheat, overcharge,
overcurrent