


## Universal Car Alarm Pro TX-I68





DC12 or 24V rechargeable Car Alarm for the cigarette lighter socket

- DC12 or 24V external siren for engine compartment for more attention
- Button for panic alarm (about 105dB)
- 1x USB-C charging port with a total of 5V / 3.0A output power
- 1x USB charging port with a total of 5V / 2.4A output power
- Automatic alarm triggering at motion detection by PIR sensor
- Car Alarm and exernal siren each about 105dB
- Possibility to connect up to 3 remote controls
- Easy handling and installation





## **Technical specifications**

- Detecting range: 120° cone angle
- Distance IR remote control ~10m (open field)
- Alarm time: Car alarm max. 2min; Siren max. 30s
- Built-in rechargeable 500mAh lithium polymer battery 3.7V
- · Charging time ~2 hours / Working time ~7 days / Standby ~14 days
- Input voltage Car alarm / Siren: DC12 or 24V
- Operating current (siren): 100mA
- Cable length of siren 1.5m
- Transmission frequency: 2.4GHz / Type: ASK
- Maximum radiated transmission power: 15.85mW
- Material: ABS
- Operating temperature: -10°C +50°C
  Weight/Dimensions (car alarm):
- 69 g / (L) 3.0 x (W) 3.0 x (H) 13.5 cm
- Weight/Dimensions (external siren): 120 g / (L) 7.3 x (W) 5.7 x (H) 6.2 cm
- Weight/Dimensions (remote control): 16 g / (L) 5.9 x (W) 3.7 x (H) 1.0 cm

## **Package Contents:**

Car Alarm, External Siren with connection cable and 3A Fuse, Remote Control (with CR2032 battery), Mounting material, User Manual

