

10 000 mAh Powerbank with fast charge

DELTAACO

A NORDIC BRAND

- 3 A / 18 W
- Charge up to 2 devices
- Short circuit protection



PRODUCT DATA

Features:	Digital battery level indicator
Capacity:	10 000 mAh / 37 Wh
Safety:	Internal temperature sensor, Over-charge-, over-discharge-, over-current- and short circuit protection.
Battery cell:	Li-ion polymer
Power bank recharge time:	USB Micro-B: ≤ 7 hours @ 5 V DC / 2 A, USB-C: ≤ 6 hours @ 5 V DC / 2.4 A or ≤ 3.5 hours @ 12 V DC / 1.5 A.
Input:	USB Micro-B: 5 V DC / 2.4 A, 9 V / 2 A or 12 V / 1.5 A USB-C: 5 V DC / 2.4 A, 9 V / 2 A or 12 V / 1.5 A
Max input:	18 W
Output:	USB-A: 5 V DC / 3 A, 9 V / 2 A or 12 V / 1.5 A USB-C: 5 V DC / 3 A, 9 V / 2 A or 12 V / 1.5 A
Max total output:	18 W

LOGISTICS DATA

Article number:	PB-C1000
Brand:	DELTAACO
EAN code:	7333048044228
Country of origin:	China
Custom tariff number:	85076000
Master carton packing unit:	20 pcs
Master carton gross weight:	6.45 kg
Master carton dimensions:	350 x 280 x 240 mm
Package type:	Box
Package weight:	270 g
Package dimensions:	120 x 200 x 30 mm

PACKAGING

Package contents:	Power bank, Micro USB charging cable and manual.
-------------------	--



SE E-post: data@deltaco.se
FI Sähköposti: info@deltaco.fi
DK E-mail: info@deltaco.dk
NO E-mail: info@deltaco.no

Tel: +46 (0) 8 555 76 200
Puh: +358 (0) 20 7120390
Tel: +45 3886 9171
Tel: +47 22 830 906

Fax: +46 (0) 8 555 76 219
Faksi: +358 (0) 20 7120399
Fax: +45 3886 9177
www.deltaco.se