

20 000 mAh Powerbank with 60 W fast charge

DELTAACO
A NORDIC BRAND

- 3 A / 66 W
- Charge up to 3 devices
- Short circuit protection



PRODUCT DATA

Features:	Digital battery level indicator
Capacity:	20 000 mAh / 74 Wh
Safety:	Internal temperature sensor, Over-charge-, over-discharge-, over-current- and short circuit protection.
Battery cell:	Li-ion polymer
Power bank recharge time:	USB Micro-B: ≤ 8 hours @ 9 V DC / 2 A ≤ 4 hours @ 12 V DC / 1.5 A USB-C: ≤ 2 hours @ 20 V DC / 3 A.
Input:	USB Micro-B: DC 5 V / 2 A, 9 V / 2 A or 12 V / 1.5 A, USB-C: DC 5 V / 3 A, 9 V / 3 A, 12 V / 3 A, 15V / 3 A or 20 V / 3 A.
Max input:	60 W
Output:	1x USB-A, max 18 W, 1x USB-A, max 18 W, 1x USB-C, 3 A, max 60 W.
Max total output:	66 W

LOGISTICS DATA

Article number:	PB-C1003
Brand:	DELTAACO
EAN code:	7333048045195
Country of origin:	China
Custom tariff number:	85076000
Master carton packing unit:	10 pcs
Master carton gross weight:	5.21 kg
Master carton dimensions:	450 x 150 x 240 mm
Package type:	Box
Package weight:	460 g
Package dimensions:	120 x 200 x 40 mm

PACKAGING

Package contents:	Power bank, USB-C to USB-C cable and manual.
-------------------	--



SE E-post: data@deltaco.se
FI Sähköposti: info@deltaco.fi
DK E-mail: info@deltaco.dk
NO E-mail: info@deltaco.no

Tel: +46 (0) 8 555 76 200
Puh: +358 (0) 20 7120390
Tel: +45 3886 9171
Tel: +47 22 830 906

Fax: +46 (0) 8 555 76 219
Faksi: +358 (0) 20 7120399
Fax: +45 3886 9177
www.deltaco.se