



WL 1025

technoline CO2 measuring device with colored air quality icons

- Display of measured CO2 value and Co2 trend indicator
- 24 hour history of measured CO2 values displayed on bar diagram
- Alarm function for high CO2 values
- Calibration option for CO2 measuring
- Current CO2 concentration in the air is display as air quality icons in traffic lights coloration: EXCELLENT, GOOD, MEDIUM, POOR (starts flashing at 2001 ppm to signal very poor air)

additional functions:

- Indoor temperature display in °C or °F
- Indoor humidity display
- MIN/MAX memory of CO2, temperature and humidity
- Quartz clock
- 12/24 h time display
- Alarm
- Low power indicator of built-in rechargeable battery
- 4 display brightness levels selectable
- Table standing

SPECIFICATIONS

Dimensions (WxHxD): 81 x 81 x 24 mm

Power supply: USB cable (included)

Internal recharge-able battery (built in with approx. 6 hours battery life)

Temperature measuring range: -9,9 - 50°C

Humidity measuring range: 1-99%

EAN: 4029665410258

