



WL 1028

Indoor climate station

- CO2 display for monitoring indoor air quality
- Powerful CO2 sensor with measuring range of up to 5000 ppm
- Ventilation recommendation based on CO2 concentration in the air (coloured display elements)
- CO2 history diagram for up to 24 hours
- Adjustable alarm for too high or too low CO2 value with optional acoustic alarm
- Quartz clock
- Alarm
- Indoor temperature display
- Indoor humidity display
- Rechargeable battery with runtime of up to 20 hours
- Wall mounting or table standing

Specifications

Station WL 1028

Dimensions (WxHxD): 161 x 115 x 25 mm

Power: USB power cable (included),
built in rechargeable battery (included)

Temperature measuring range:

-9,9°C to 49,9°C

Humidity measuring range: 1% to 99%

CO2 measuring range: 400 to 5000 PPM

Ventilation recommendations as traffic light representation:



EAN: 4029665110288