

MIDLAND G18 Pro duo set

Radio with 16 PMR446 channels



Art.-No.: C1145.S1

Technical details:

- 16 channels (81 preset)
- LC display with background light
- VOX, 10 levels
- 50 CTCSS coding sounds / 105 DS identification sounds
- Scrambler
- Adjustable transmission power
- Voice announcement
- Squelch
- Monitor, alarm and SOS function
- Comander (programmable with software)
- FM Radio (programmable with software)
- Connector: Motorola
- Colour: black
- Weight: 240g (incl. battery)
- Measurements: 113 x 56 x 38mm

Scope of delivery: each item twice radio G18 Pro, MA 25-M speaker microphone, desktop charger, charging cable, Li-Ionen battery pack (1600 mAh), beltclip

- rugged and compact design
- tested to military standard MIL-STD810G
- handsfree function (VOX)
- IP67 waterproof
- 19 hours operating time

A radio specially made for demanding user. No matter what challenge this radio is facing, it won't back down! It's the ideal partner for rough day-to-day work and includes all the features necessary to get the job done.

Thanks to the Scrambler function and the CTCSS/DCS coding your conversations are decoded and can only be accessed by the same working group.

The handsfree mode is made for situations, where both hands are needed. The built-in time-out-timer limits the max. transmission time and prevents unintentional messages.

Optional accessories:

- Battery pack Li-Ion 1600mAh for G15, G18, Arctic, Art.-No.: C1128
- MA 25-M speaker microphone, Art.-No.: C1129
- MA 31-M security headset, Art.-No.: C732.06
- MA 27-M headset, Art.-No.: C1130
- PRG-G15 programming kit, Art.-No.: C1131
- 6-way desktop multi-charger, Art.-No.: C1251

Alan Electronics GmbH