

RGB FM Transmitter FMT 1600BT



Kabellose Audioübertragung /
Wireless audio transmission



Freisprechfunktion /
Hands free calling function



Musikwiedergabe von USB-Datenträger /
USB Drive audio player



Sprachassistent kompatibel /
Voice assistant support



Bluetooth V5.0



RGB RGB Licht / Light



USB-C PD 20W



USB QC3.0



- Wireless audio transmission to car stereo system by FM channel
- USB charging with QC3.0
- USB-C PD 20W charging
- USB drive music playback up to 64 GB
- RGB colour light mode
- Hands free Bluetooth calling
- Echo cancellation and noise suppression technology
- Voice assistant support
- Car voltage display

Technical specifications:

- Input voltage DC 12V ~ 24V
- Bluetooth version V 5.0
- Bluetooth distance < 10m
- Bluetooth frequency 2.4GHz
- Radiated transmission power max. 2.5mW
- USB drive port (🎵) power ≤ 5V / 1A
- USB QC3.0 port output power 5V / 3.0A, 9V / 2.0A, 12V / 1.5A
- USB-C PD port output power 5V / 3.0A, 9V / 2.2A, 12V / 1.66A
- USB drive capacity Max. 64GB
- Supported audio format MP3 / WMA / WAV / FLAC
- RGB lightred, yellow, green, sky-blue, blue, purple, rainbow
- Voice assistant compatibility Google Assistant, iOS 8, Android 9.0, EMUI 11
- FM frequency range 87.5 - 108.0MHz
- FM transmission distance < 5 m
- Distortion < 0.1% / SNR > 85 dB
- Operating temperature -10 °C up to 50 °C

Package contents:

Technaxx FMT1600BT, user manual

Art. № 4969

