

FullHD 1080p Projector TX-177



FullHD-resolution 1080P



Projection size from 50" to 200"



3 Watt speaker



LED lifetime up to 40,000 hours



2x HDMI, USB, SD, AV, VGA, AUX



Remote control



Native 1080p projector with multimedia player
Projection size from 50" to 200"
Integrated 3 Watts speaker
Manual focus adjustment
Long LED lifetime 40,000 hours
Connectable with Computer/Notebook, Tablet, Smartphone and Gaming consoles via AV, VGA, or HDMI
Playback of Video, Photo and Audio Files from USB, SD or external hard disk
Usable with Remote Control

Technical specifications:

- Projection technic: LCD LED projection system
- Lens: Multichip composite coating optical lens
- Power: AC 100 - 240 V~, 50/60 Hz
- Projector consumption / brightness: 70 Watt / 15000 Lumen
- Standby power consumption: 1.3 Watt
- Projection size / distance: 50" - 200" / 1.6 - 6.2 m
- Contrast ration / Display colours: 1500:1 / 16.7 M
- Lamp colour temperature / lifetime: 9000K / 40000 hours
- Keystone correction: Optical $\pm 15^\circ$ (horizontal)
- Signal ports:
 - AV input (1. OVp-p $\pm 5\%$, 480i, 576i)
 - VGA input (480i, 480p, 576i, 576p, 720p, 1080i, 1080p)
 - HDMI input (480i, 480p, 576i, 576p, 720p, 1080i, 1080p)
 - AUX output (3.5 mm)
- Native resolution: 1920 x 1080 pixel
- Aspect ratio: 4:3 / 16:9 / Auto
- Audio speaker: 3 Watt
- USB / SD card / external hard disk format:
 - Video: MPEG1, MPEG2, MPEG4, RM, AVI, RMVB, MOV, MKV, FLV, VOB, MPG, ASF
 - Music: WMA, MP3, M4A(AAC)
 - Photo: JPEG, BMP, PNG, GIF
- USB / SD card: max. 1 TB
- External hard disk: max. 2 TB
- USB Power Supply: 5 V, 0.5 A (Max.)
- Weight / Dimensions :1360 g / (L) 23.4 x (W) 18.7 x (H) 9.6 cm

Compatibility:

Digital camera, TV-Box, PC / Notebook, Smartphone, Game console, USB-Device, SD card, external hard disk, Amplifier.

Package Contents:

Technaxx[®] FullHD 1080p Projector TX-177, AV signal cable, remote control (2x AAA included), HDMI cable, power cable, user manual

Article-No. 4971

