

TYPE HP118

TERMOVENTILATORE PTC
PTC FAN HEATER
220-240 V~ 50 Hz 1800W



LEFT-RIGHT
OSCILLATION



OSCILLAZIONE
DX/SX

ADJUSTABLE
THERMOSTAT



TERMOSTATO
REGOLABILE

2 HEATING
POWERS



2 POTENZE DI
RISCALDAMENTO

VENTILATION
FUNCTION



FUNZIONE
VENTILAZIONE

WARNING LIGHT



SEGNALATORE
LUMINOSO



- Termoventilatore con resistenza ceramica PTC: eroga potenza in base alla temperatura ambiente (bassa temp. = Potenza massima, e viceversa).
- Selezioni: 0 / Ventilazione / Eco (900W) / Rapid (1800W).
- Termostato ambiente regolabile.
- Oscillazione automatica Destra / Sinistra.
- Spia luminosa
- Interruttore anti-ribaltamento.
- Corpo in plastica con maniglia integrata, griglia frontale in metallo.
- Adatto per ambienti di 18 m² circa.



- Fan heater with PTC ceramic resistance: delivers power based on the environment temperature (low temp. = Maximum power, and vice versa).
- 0 / Ventilation / Eco (900W) / Rapid (1800W) selections.
- Adjustable room thermostat.
- Right / Left automatic oscillation.
- Signal lamp.
- Tip-over switch.
- Plastic body with integrated handle, metal front grille.
- Suitable for rooms of approximately 18 m².