

TYPE HP119

TERMOVENTILATORE PTC INDUSTRIALE INDUSTRIAL PTC FAN HEATER

220-240 V~ 50 Hz 3000 W



ADJUSTABLE
THERMOSTAT



TERMOSTATO
REGOLABILE

2 HEATING
POWERS



2 POTENZE DI
RISCALDAMENTO

VENTILATION
FUNCTION



FUNZIONE
VENTILAZIONE

WARNING LIGHT



SEGNALATORE
LUMINOSO

3000w



- Termoventilatore con resistenza ceramica PTC: eroga potenza in base alla temperatura ambiente (bassa temp. = Potenza massima, e viceversa).
- Selezioni: 0 / Ventilazione / Eco (1500W) / Rapid (3000W).
- Termostato ambiente regolabile.
- Spia luminosa
- Interruttore anti-ribaltamento.
- Corpo in plastica con maniglia superiore, griglia frontale in metallo.
- Adatto per ambienti di 30 m² circa.



- Fan heater with PTC ceramic resistance: delivers power based on the environment temperature (low temp. = Maximum power, and vice versa).
- 0 / Ventilation / Eco (1500W) / Rapid (3000W) selections.
- Adjustable room thermostat.
- Signal lamp.
- Tip-over switch.
- Plastic body with top handle, metal front grille.
- Suitable for rooms of approximately 30 m².