

TYPE HP126

TERMOVENTILATORE PTC A COLONNA WIFI WI-FI PTC FAN HEATER

220-240V~ 50Hz 2000W



2 HEATING
POWERS



2 POTENZE DI
RISCALDAMENTO

ADJUSTABLE
THERMOSTAT



TERMOSTATO
REGOLABILE

VENTILATION
FUNCTION



FUNZIONE
VENTILAZIONE

LEFT-RIGHT
OSCILLATION



OSCILLAZIONE
DX/SX

REMOTE CONTROL
INCLUDED



TELECOMANDO
INCLUSO



GUARDA
IL VIDEO



- Termoventilatore con resistenza ceramica PTC, eroga potenza in base alla temperatura ambiente: bassa temperatura = max potenza, e viceversa.
- APP compatibile iOS e Android per il controllo, con Wi-Fi (2.4-5) GHz, di ogni funzione e per la programmazione quotidiana e settimanale.
- E' possibile condividere il dispositivo con più persone contemporaneamente.
- Controllo vocale compatibile con Amazon Alexa e Google Assistant.
- Comandi elettronici a sfioro e telecomando.
- Display visualizza Temperatura, Tempo, e ogni Funzione.
- Modalità Automatica / Manuale.
- Selezione automatica della potenza in base alla temperatura da conseguire.
- Selezione Ventilazione/ Eco (1000W)/ Rapid (2000W).
- Termostato ambiente regolabile 15°- 40°C.
- Timer 1-12h.
- Oscillazione automatica Destra / Sinistra.
- Tasto Stand-by/ON
- Interruttore 0-I.
- Interruttore anti-ribaltamento.
- Corpo in plastica con maniglia integrata.
- Grado di protezione IP20.
- Idoneo per ambienti di 20m² circa.



- Fan heater with PTC ceramic resistance, delivers power based on the environment temperature: low temperature = max power, and vice versa.
- iOS and Android compatible APP for the control, with (2.4-5) GHz Wi-Fi, of each function and for daily and weekly programming.
- It is possible to share the device with several people at the same time.
- Voice control compatible with Amazon Alexa and Google Assistant.
- Electronic touch controls and remote control.
- Display shows Temperature, Time, and each Function.
- Automatic / Manual Mode.
- Automatic power selection based on the temperature to be achieved.
- Ventilation / Eco (1000W) / Rapid (2000W) selection.
- 15°-40°C adjustable room thermostat.
- 1-12h timer.
- Right / Left automatic swing.
- Stand-by / ON button.
- 0-I switch.
- Tip-over switch.
- Plastic body with integrated handle.
- IP20 degree of protection.
- Suitable for rooms of about 20m².