



Type.....

57956

Designation .....

High Speed GaN Charger 65W

Housing material:.....

PC

Housing colour: .....

White

**Dimensions:**

Length .....

108.2 ± 1mm

Width .....

34.4 ± 1mm

Height .....

28 ± 1mm

Weight .....

137 ± 3g

**Charger:**

Input: .....

100 – 240V 50/60Hz 1.5A max.

AC Plug: .....

EU Plug

**No publication or circulation of data to third parties without consent of VARTA Consumer Batteries**

<b>No load Power consumption</b>	<300mW	
<b>Efficiency</b>	>81.39% @ 5V Output >86.62% @ 9V Output >87.4% @ 12V Output	
<b>Output:</b>	<b>Voltage/Current</b>	<b>Wattage</b>
<b>USB Type C PD 1:</b>	5.0V 3.0A   9.0V 3.0A   12.0V 3.0A   15.0V 3.0A   20.0V 3.25A	65W max. (single output)
<b>USB Type C PD 2:</b>	5.0V 3.0A   9.0V 3.0A   12.0V 3.0A   15.0V 3.0A   20.0V 3.25A	65W max. (single output)
<b>USB-A QC:</b>	5.0V 3.0A   9.0V 3.0A   12.0V 2.5A   20.0V 1.5A	30W max. (single output)
<b>USB-Type C PD 1 + 2:</b>	USB C PD 1: 5.0V 3.0A   9.0V 3.0A   12.0V 3.0A   15.0V 3.0A + USB C PD 2: 5.0V 3.0A   9.0V 2.22A   12.0V 1.67A	45W (USB C PD 1) + 20W (USB C PD 2) 65W max. (shared)
<b>USB-Type C PD 1 + USB A QC:</b>	USB C PD 1: 5.0V 3.0A   9.0V 3.0A   12.0V 3.0A   15.0V 3.0A + USB A QC: 5.0V 3.0A   9.0V 2.0A   12.0V 1.5A	45W (USB C PD 1) + 18W (USB A QC) 63W max. (shared)
<b>USB-Type C PD 2 + USB A QC:</b>	USB C PD 2: 5.0V 1.5A + USB A QC: 5.0V 1.5A	7.5W (USB C PD 2) + 7.5W (USB A QC) 15W max. (shared)
<b>USB-Type C PD 1 + USB-Type C PD 2 + USB A QC:</b>	USB C PD 1: 5.0V 3.0A   9.0V 3.0A   12.0V 3.0A   15.0V 3.0A + USB C PD 2: 5.0V 1.5A + USB A QC: 5.0V 1.5A	45W (USB C PD 1) + 7.5W (USB C PD 2) + 7.5W (USB A QC) 60W max. (shared)

**Output shut down:** ..... Overload protection if current is >5-15% over each individual USB port current limit (refer to the above-mentioned current limits) or over 65W. Short circuit protection.

**No publication or circulation of data to third parties without consent of VARTA Consumer Batteries**