


OOLIGHT


USER MANUAL



imini

The imini is a quick-release keychain flashlight.

PACKAGE CONTENTS



imini




LR41 Button Cells

SPECIFICATIONS

| | | |
|------------|----------------------------------|-------|
| 10lumens | | 30min |
| | | |
| 27cd | 1.5m | IPX6 |
| 10m | | |
| LENGTH | 35mm / 1.38in | |
| BODY DIAM. | 13.8mm / 0.54in | |
| WEIGHT | 11.3g / 0.40oz (incl. Batteries) | |


INSULATING FILM

Before first use, please detach the flashlight from the magnetic cap, unscrew the magnetic base and then remove the insulating film.



BATTERY INSTALLATION

If the button coin cell batteries need to be replaced, make sure that the positive end of the new batteries faces the flashlight head when you insert them.





*While replacing the batteries, please keep the magnetic base away from the magnetic cap. Should the base have been caught in the magnetic cap, please screw the battery housing into the magnetic cap tightly so that you can take the flashlight out.

AVAILABLE BATTERIES

- 3 * LR41 Button Coin Cell Battery

TURN ON/OFF



PLEASE REPLACE THE BATTERIES ONCE THEY RUN OUT, AVOIDING THE RISK OF ELECTROLYTE LEAKAGE.

KEEP THE PRODUCT OUT OF REACH OF CHILDREN. IT MAY CAUSE CHOKING HAZARDS.

PLEASE STORE OR DISPOSE OF THE USED BATTERIES WITH CARE AFTER REPLACING THEM. BUTTON CELLS ARE DANGEROUS IF SWALLOWED, IN PARTICULAR, BY CHILDREN.

DANGER

- DO NOT shine the light directly into human eyes. This may cause temporary blindness, or permanent damage to the eyes.

CAUTION

- While unscrewing the magnetic base to replace batteries, DO NOT let it get into contact with any other magnet. Otherwise, the insulating pole inside the base may be lost.
- DO NOT power on the flashlight by mixing used and new batteries or batteries of different brands together.
- The brightness and runtime of the flashlight may decrease when the working temperature for the installed batteries is below 0 C.
- DO NOT short-circuit the batteries.
- DO NOT clean the lens with alcohol or any other chemicals.

EXCLUSION CLAUSE

Olight is not liable for damages or injuries sustained resulting from the usage of the product inconsistent with the warnings in the manual.

CONTENTS

| | |
|------------------------|----|
| (EN) English | 01 |
| (CN) 简体中文 | 01 |
| (FI) Finnish | 01 |
| (NO) Norwegian | 01 |
| (SV) Swedish | 01 |
| (NL) Nederlands | 01 |
| (PL) Polska | 01 |
| (DE) Deutsch | 01 |
| (HU) Magyarország | 02 |
| (RU) Русский | 02 |
| (ES) Español | 02 |
| (RO) Romanesc | 02 |
| (UA) Ukrainian | 02 |
| (JP) 日本語 | 03 |
| (KR) 한국어 | 03 |
| (TH) ไทย | 03 |
| (FR) Français | 03 |
| (IT) Italia | 03 |
| (SK) Slovenský jazyk | 03 |
| (PT) Português | 03 |

(EN) English

Turn on by detaching the body from the magnetic cap. Turn off by attaching it back onto the magnetic cap.

(CN) 简体中文

将手电与磁吸尾盖分离即亮，吸附上即灭。

(FI) Finnish

Kytke valo päälle irrottamalla se magneettisesta korkista. Kiinnitä korki takaisin sammuttaaksesi valon.

(NO) Norwegian

Slå på ved å fjerne kroppen fra magnetetten. Slå av ved å feste den tilbake på magnetetten.

(SV) Swedish

Tänd lampan genom att ta bort lampan från magnetlocket. stäng av genom att sätta tillbaka den på magnetlocket.

(NL) Nederlands

Schakel het licht aan door de behuizing van de magnetische dop te verwijderen. Zet hem uit door hem weer op de magnetische dop te bevestigen.

(PL) Polska

Aby włączyć, odłącz latarkę od magnetycznego uchwyty. Podłącz go ponownie, aby wyłączyć latarkę.

(DE) Deutsch

Zum Einschalten den Lampenteil von der Magnethalterung entfernen. Zum Ausschalten den Lampenteil wieder an der Magnethalterung anbringen.

(HU) Magyarország

A bekapcsoláshoz távolítsa el a lámpatestől a mágneses kupakot. A kikapcsoláshoz helyezze vissza a lámpatestre a mágneses kupakot.

(RU) Русский

Включите, сняв корпус с магнитного колпачка. Выключите, прикрепив его обратно на магнитный колпачок.

(ES) Español

Encienda la linterna quitando la tapa magnética y apáguela poniéndola de nuevo.

(RO) Romanesc

Porniți prin îndepărtarea corpului de pe capacul magnetic. Opritiți atașându-l înapoi pe capacul magnetic.

(UA) Ukrainian

Для того, щоб увімкнути ліхтарик, зніміть магнітний ковпачок з корпусу. Для того, щоб вимкнути ліхтарик, прикріпіть його назад до корпусу.

(JP) 日本語

マグネットキャップを本体から外すと点灯し、本体にマグネットキャップに取り付けると、消灯します。

(KR) 한국어

자석 캡에서 몸체를 분리시켜 전원을 켭니다. 자석캡에 다시 붙이면 전원은 꺼집니다.

(TH) ไทย

เปิดโดยถอดตัวเครื่องออกจากฝาแม่เหล็ก ปิดโดยติดกลับเข้ากับแม่เหล็ก

(FR) Français

Allumez la lampe en retirant le corps du capuchon magnétique. Éteignez la lampe en le refixant sur le capuchon magnétique.

(IT) Italia

si accende rimuovendo il corpo dal cappuccio magnetico. Si spegne riattaccandolo al cappuccio magnetico.

(SK) Slovenský jazyk

Zapnete odstránením tela z magnetického uzáveru. Vypnete ho nasadením späť na magnetický uzáver.

(PT) Português

Ligue removendo o corpo da tampa magnética. Desligue encaixando a tampa magnética de volta.

WARRANTY

Within 30 days of purchase: Contact the original seller for repair or replacement.

Within 2 years of purchase: Contact Olight for repair or replacement.

This warranty does not cover normal wear and tear, modifications, misuse, disintegrations, negligence, accidents, improper maintenance, or repair by anyone other than an authorized retailer or Olight itself.

EU-DECLARATION OF CONFORMITY



EU-Declaration of Conformity can be found here: <https://olightworld.com/ec-declaration>

USA Customer Support

cs@olightstore.com

Global Customer Support

customer-service@olight-world.com

Visit www.olightworld.com to see our complete product line of portable illumination tools.

OOLIGHT

Dongguan Olight E-Commerce Technology Co., Ltd

4th Floor, Building 4, Kegou Industrial Park, No 6 Zhongnan Road, Changan Town, Dongguan City, Guangdong, China. Made in China

RoHS
3.4000.0415 A. 13. 06. 2022

THANK YOU!