

Green Cell

GC Power Inverter

Product card



Specification:

Model:	INV04DE
Input voltage [V]:	24V
Output Power/Peak Power:	500W / 1000W
Sine Wave:	Modified
Socket type:	F
Fuse Rating [A]:	30A
Number of fuses:	2
Current consumption without load [A]:	0,6A
No-load power consumption:	14,4A
Efficiency at a load of approx. 90% of the rated power:	85%
Dimensions (LxWxH):	18,9 x 10,6 x 6,0 cm
Dimensions with mounting bracket:	19,6 x 10,6 x 6,2 cm
Weight (g):	843g
Cross-section of cables included in the kit (mm ^ 2):	6
Number of wire pairs included in the kit:	1