

Green Cell

GC Power Inverter

Product card



Specification:

Model:	INV06
Input voltage [V]:	12V
Output Power/Peak Power:	150W
Sine Wave:	Modified
Socket type:	F
Fuse Rating [A]:	30A
Number of fuses:	1
Current consumption without load [A]:	0,5A
No-load power consumption:	6A
Efficiency at a load of approx. 90% of the rated power:	85%
Dimensions (LxWxH):	13,1 x 10,6 x 6,0 cm
Dimensions with mounting bracket:	13,8 x 10,6 x 6,2 cm
Weight (g):	587g
Number of wire pairs included in the kit:	1 with car plug 12VDC