

Green Cell

GC Power Inverter

Product card



Specification:

Model:	INV10
Input voltage [V]:	12V
Output Power/Peak Power:	2000W / 4000W
Sine Wave:	Modified
Socket type:	F
Fuse Rating [A]:	30A
Number of fuses:	6
Current consumption without load [A]:	1,3A
No-load power consumption:	15,6A
Efficiency at a load of approx. 90% of the rated power:	85%
Dimensions (LxWxH):	31,5 x 17,8 x 7,6 cm
Dimensions with mounting bracket:	32,7 x 17,8 x 7,8 cm
Weight (g):	3772g
Cross-section of cables included in the kit (mm ^ 2):	10
Number of wire pairs included in the kit:	2