

Green Cell

GC Power Inverter

Product card



Specification:

Model:	INV12
Input voltage [V]:	12V
Output Power/Peak Power:	3000W / 6000W
Sine Wave:	Modified
Socket type:	F
Fuse Rating [A]:	30A
Number of fuses:	6
Current consumption without load [A]:	1,7A
No-load power consumption:	20,4A
Efficiency at a load of approx. 90% of the rated power:	85%
Dimensions (LxWxH):	37,0 x 20,9 x 9,3 cm
Dimensions with mounting bracket:	38,7 x 20,9 x 9,5 cm
Weight (g):	5126g
Cross-section of cables included in the kit (mm ^ 2):	16
Number of wire pairs included in the kit:	2