

**Green Cell**

# GC Power Inverter

## Product card



### Specification:

<b>Model:</b>	INV17
<b>Input voltage [V]:</b>	24V
<b>Output Power/Peak Power:</b>	500W / 1000W
<b>Sine Wave:</b>	Pure
<b>Socket type:</b>	F
<b>Fuse Rating [A]:</b>	30A
<b>Number of fuses:</b>	2
<b>Current consumption without load [A]:</b>	0,35A
<b>No-load power consumption:</b>	8,4A
<b>Efficiency at a load of approx. 90% of the rated power:</b>	85%
<b>Dimensions (LxWxH):</b>	22,0 x 10,6 x 6,0 cm
<b>Dimensions with mounting bracket:</b>	22,5 x 10,6 x 6,2cm
<b>Weight (g):</b>	1090g
<b>Cross-section of cables included in the kit (mm ^ 2):</b>	6
<b>Number of wire pairs included in the kit:</b>	1 + 1 with car plug 12VDC