

Green Cell

GC Power Inverter

Product card



Specification:

Model:	INV25
Input voltage [V]:	24V
Output Power/Peak Power:	1500W / 3000W
Sine Wave:	Modified
Socket type:	F
Fuse Rating [A]:	30A
Number of fuses:	6
Current consumption without load [A]:	1,38A
No-load power consumption:	16,56A
Efficiency at a load of approx. 90% of the rated power:	85%
Dimensions (LxWxH):	27,0 x 17,8 x 7,6 cm
Dimensions with mounting bracket:	28,7 x 17,8 x 7,8cm
Weight (g):	2844g
Cross-section of cables included in the kit (mm ^ 2):	10
Number of wire pairs included in the kit:	1