

**Green Cell**

# GC Power Inverter

## Product card



### Specification:

<b>Model:</b>	INVGC01
<b>Input voltage [V]:</b>	12V
<b>Output Power/Peak Power:</b>	300W / 600W
<b>Sine Wave:</b>	Modified
<b>Socket type:</b>	F
<b>Fuse Rating [A]:</b>	40A
<b>Number of fuses:</b>	1
<b>Current consumption without load [A]:</b>	0,5A
<b>No-load power consumption:</b>	6A
<b>Efficiency at a load of approx. 90% of the rated power:</b>	90%
<b>Dimensions (LxWxH):</b>	18,0 x 10 x 6 cm
<b>Dimensions with mounting bracket:</b>	18,5 x 10 x 6,0 cm
<b>Weight (g):</b>	724g
<b>Cross-section of cables included in the kit (mm ^ 2):</b>	12AWG
<b>Number of wire pairs included in the kit:</b>	1 + 1 with car plug 12VDC