



## FEATURES

- 2 Speed precision turntable with metal alloy platter (33 1/3 and 45 rpm).
- Auto-Stop and Auto Rotation Speed Control System.
- High Torque Rotary Motor with belt drive transmission system.
- Adjustable counterweight for tonearm balancing.
- Anti-Skating Tone Arm with soft damping lifter mechanism.
- High Quality AT3600L moving magnet stylus with aluminium Cartridge Headshell.
- Wireless transmitter to use any Bluetooth speaker for Audio Output (Stereo) with 10M range.
- USB-Port for connection to PC or MAC for professional audio recording (USB Cable and Software included).
- Built In Audio Pre-Amp (with RIAA EQ) for direct LINE-IN Connection to any standard amplifier.
- Pre-Amplifier ON/OFF Switch enables connection to PHONO Amplifier input.
- Wired Connection using RCA Audio Output Terminal Jacks (Stereo)
- Crystal Polymer Touch Control Panel with white LED Ambient Back-Lighting.
- Avant Garde Brushed aluminium body.
- 45rpm Spindle Adaptor (for EP size records) included.
- Heavy duty soft silicone rubber platter mat.
- Built In AC Power supply 230V.
- Dimension: 430 x 368 x 116 mm.
- Weight: 5,1 Kg.
- Accessories included: IB manuals, AC cable, PC or MAC recording usb cable & software cd, Stereo Audio RCA cable(1,2 m), Silicone rubber Pad, Leatherette dust cover..

## PACKAGING

**SKU:**  
APX-680BT



**EAN:**  
8435256897500



**MASTER BOX:**  
1



**BOX SIZE (L x W x H):**  
51x40x18 cm



**WEIGHT:**  
6



**INNER BOX:**  
NA

## MULTIPLE COLORS

**SKU:** APX-680BT/WT **EAN:** 8435256898019

