



FEATURES

- Luxurious Leatherette and Metallic Titanium Finishing.
- Bluetooth 5.0 Audio Receiver works with all mobile devices.
- Wireless Range: 10m (30 Ft.).
- USB-Port for direct MP3 playback 32GB (FAT).
- AUX in RCA jacks for external device playback.
- HDMI-Port with ARC (Audio Return Channel) Function& CEC.
- OPTICAL Input Port for digital audio connectivity.
- FM-PLL Radio tuner with telescopic metal antenna.
- High Power Audio output: 50W RMS.
- Compressed Wood Cabinet for Deeper Bass Resonance.
- Full Dynamic Range: 1 x 4" Bass Woofer and 2 x 3" High Frequency Drivers.
- Independent Bass and Treble Controls.
- LED Digital Clock with 24-Hour time format.
- Metal rotary Volume Knob with tactile feedback.
- Wireless Remote controller for the main functions.
- ECO-Friendly Power Supply for reduced STANDBY power consumption = 1W.
- AC Operation: AC 230 / 240 ~ 50 HZ.
- Accessories included: Power cable, remote control ,2 batteries LR03 /RCA to AUX IN 3.5 mm Stereo Plug Cable, User manual
- Dimensions: 305 x 170 x 175 mm.
- Weight: 320g.

PACKAGING

SKU:
BSTU-750BR



EAN:
8435256897746



MASTER BOX:
2



BOX SIZE (L x W x H):
46x36x25 cm



WEIGHT:
1



INNER BOX:
1

MULTIPLE COLORS

