

LEATHERETTE WIRELESS SPEAKER WITH BLUETOOTH AND FM



- Luxurious Leatherette and Metallic Titanium Finishing.
- Bluetooth 5.0 Audio Receiver works with all mobile devices.
- Wireless Range: 10m (30 Ft.).
- HDMI-ARC (Audio Return Channel) Port for TV/DVD/BluRay connectivity.
- OPTICAL Input Port for digital audio connectivity
- 6.3mm Microphone / Guitar input jack.
- USB-Port for direct MP3 playback.
- Stereo 3.5mm AUX-in jack for external device playback.
- Stereo Earphone jack (3.5mm) Built IN.
- FM-PLL digital tuner with telescopic metal antenna.
- High Power Audio output: 50W RMS.
- Compressed Wood Cabinet for Deeper Bass Resonance.
- Full Range Frequency Response : 45Hz - 20KHz.
- 4000 MAH Lithium Rechargeable Battery.
- Rotary Volume Knob with tactile feedback
- Ambient lighting 2 buttons.
- Independent Bass and Treble Controls.
- Built-in ECO-Friendly Power Supply with low STANDBY power consumption.
- Easy Handle To Carry.
- Wireless Remote controller included.
- AC Operation: AC 230 / 240 ~ 50 HZ.
- Accessories included: Power cable, remote control, 2 alkaline aiwa batteries AAA(LR03), Aux cable 3.5mm to 3.5mm.
- Dimensions: 265 x 165 x 159 mm.
- Weight: 3.3 Kg.

PACKAGING

SKU:
BSTU-800BK



EAN:
8435256897128



MASTER BOX:
2



BOX SIZE (L x W x H):
46x36x25 cm



WEIGHT:
1



INNER BOX:
1

MULTIPLE COLORS

