



FEATURES

- Bluetooth 5.0. Wireless Range: 10m (30 Ft.).
- USB-Port and Micro-SD-Slot for MP3 playback.
- AUX in 3.5mm Stereo Input Jack for external device connection.
- DSP with 5-Mode Preset Equalizer: Rock, Jazz, Pop, Classic, Cut.
- Independent Bass and Treble Precision Rotary Controls.
- Digital Audio Recorder Built In For MP3 Recording to USB/Micro-SD.
- High Power Audio output: 400W P.M.P.O/ 50 W RMS.
- FM radio.
- Frequency Response: 56Hz - 20KHz.
- Dual 6.5" HyperBass Drivers for Extremely Powerful Low Frequency Range.
- Dual 1" Metal-Alloy Tweeters for Optimum Clarity and High Frequency Audio.
- Ultra Sharp WHITE LED Display.
- RGB-LED Party Speaker Lighting System Built In.
- 6.3mm Microphone Input Jack Built-In.
- Secondary WIRED Dynamic Microphone Built In.
- VHF Long Range Wireless KARAOKE MIC included.
- ECHO Control with Rotary Adjustment Knob.
- Digital Audio Recorder Built In For MP3 Recording to USB/Micro-SD.
- Independent MICROPHONE Volume Rotary Control for Mic-Mixing.
- Microphone Priority Function (Auto Music Level Adjustment during Karaoke).
- External AC/DC 15V Adaptor / Charger Included (3-4 Hour Charging Time).
- Rechargeable 12V battery (3Ah, 6 Hour Playback) with Battery Level Display.
- DC-12V Input Connector for use with any 12V DC Vehicle battery.
- Wireless Remote controller included.
- Dimensions: 270 x 260 x 550 mm.
- Weight: 5.870 kg.
- Accessories included: remote control, alkaline batteries, 1 wired microphone, 1 wireless VHF microphone, AC-Adaptor, 3.5 mm to 3.5 mm Aux-in cable.

PACKAGING

SKU:
KBTUS-400



EAN:
8435256897524



MASTER BOX:
1



BOX SIZE (L x W x H):
68x32x32 cm



WEIGHT:
8.42



INNER BOX:
1

MULTIPLE COLORS

