

Product information

00 50 03 T BK

Carabiner

2 pieces



- For reliable tool protection: holding capacity tested in numerous drop tests for tools up to 6 kg, even battery-operated tools
- Twistlock: prevents unintentional opening of the carabiner

- Snapper opening: 16 mm
- Max. load capacity in longitudinal direction in locked state: 2KN
- To meet regulations while working at heights, for example industrial climbing, arborists, rescue services, at sea, etc.
- Mushroom head lock to increase tensile strength
- With pin to create an eyelet: can be inserted for a permanent connection between equipment carabiner and lanyard/adaptor strap
- Robust and light thanks to high-strength aluminium
- Snapper opening: 16 mm
- Max. static payload in longitudinal direction when locked: 2 KN
- Contents: 2 carabiners, security pins
- No PPE (personal protective equipment): not suitable for personal safety!

- Read all warnings and instructions on product and packaging carefully prior to use
- No PPE (personal protective equipment): not suitable for personal safety!
- Only for latching tools from the KNIPEX Tethered Tools range, connected and combined in accordance with tethering system instructions
- Do not use around moving or rotating equipment
- Will not support human weight
- Inspect for wear before each use. Do not use if evidence of wear.



General

Article No.	00 50 03 T BK
EAN	4003773081371
Weight	30 g
Dimensions	82 x 48 x 12 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details

Load capacity	2 KN
---------------	------

technical change and errors excepted



