# **DATASHEET**


# Circular Connector, Wire to Panel, Straight Female Plug and Panel Mount Male Socket 6 Contacts / M12


Version 10/23

Item no.: 2705563









## **Specification**

Number of Contacts: 6 Mating thread type: M12

### Material

Shell: Nickel plated Zinc Alloy Insulation: Black Bakelite Contact: Silver plated Copper

#### Electrical

Operating voltage: 48V Rated current: 1A

Insulation resistance:  $100~M\Omega$  min. Contact resistance:  $10~m\Omega$  max.

#### Environment

Operation temperature: -20 to 85°C

Protect class: IP55 Termination: Solder

Suit Cable size: O.D. ø5mm max.

Wire guide: AWG 22 - 20

Conductor cross-section: 0.34 - 0.5 mm<sup>2</sup>