



Abbildung ähnlich

**Product Features**

Basic-line splice box, extensible, 19"/1U, 12xSC-D, OS2, blue

- sheet steel housing, powder coated
- labelled ports
- with slide-in unit
- can be tilted downwards when opened
- front quick release (push-pull)
- 2 splice cassettes for holding 12 or 24 pigtails
- inserted crimp splice holder
- prepared with pigtails inserted in bundle of 12 incl. 12 x SC-D ceramic couplings
- 24 SC-fibre pigtails E9/125 µm, 2 m, SM PC, grade C
- with test protocol for all fibres incl. serial number
- 2 x PG13.5/M20 - cable glands in the back (each 2 x right/left)
- 1 x PG13.5 gland in scope of delivery
- black (similar to RAL 9005)

**Features****General**

Surface	steel sheet, powder-coated
Classification	OS2
Protection class IP	20
Halogen Free	Yes
GTIN (EAN)	4043921667101

**Mounting types**

(19-inch)-installation, 1 rack unit	Yes
-------------------------------------	-----

**Dimensions/Weights without packaging**

Length mm	482
Width mm	245
Height mm	44

**Certifications**

RoHS conform	Yes
--------------	-----

**References**

Accessories	228040502, 228040602, 228040802, 228040902, 228060500, 228060600, 228060800, 228060900, 228070000, 228070100, 228070200, 228070312
-------------	--