



Product Features

ClassEA iso-Patchpanel, shielded, surface mounting, for desktop-/wall mounting, mounting on a DIN-rail with DIN-rail mounting adapter 10010070, 12 RJ45 ports, pure white (similar RAL 9010)

- for use in 10 Gigabit-Ethernet-Networks (transmission bandwidth 500 MHz)
- DIN rail mounting with additional adapter
- protection class IP 20
- fully shielded metal housing
- quick mounting with latching lid
- RJ45 ports
- quick one step mounting of strain relief and shielding
- quick installation via LSA-contacts
- color code according to EIA/TIA 568 A and B
- UPOE conform
- HDBaseT conform
- suitable for Cat.6 and Cat.7 cables with Ø 6-10mm
- LSA-contacts for one wire 0,4-0,63 mm Ø, AWG 26-22, maximum number of connections > 50-times
- suitable for PoE++ / PPoE according to IEEE 802.3bt
- according to the following standards:
- ISO/IEC 11 801, ClassEA, shielded
- DIN EN 50173-1, ClassEA, shielded
- ANSI TIA/EIA-568-C.2, ClassEA, shielded
- DIN EN 60603-7-51, 500 MHz, shielded
- life > 750 cycles
- RJ11/RJ12-protected against mismatching

Features

General	
Surface	painted, high-gloss
Labeling field	Yes
shielded	Yes
Classification	ClassEA iso
PoweroverEthernet	Yes
Protection class IP	20
Halogen Free	Yes
Statistical goods number	85369010
Country of manufacture	DE
GTIN (EAN)	4043921666548

Mounting types	
desktop design	Yes
DIN-Rail	Yes
surface-mounted	Yes
wall installation	Yes
Dimensions/Weights without packaging	
Length mm	98
Width mm	238,5
Height mm	30,46
Certifications	
WEEE	Yes
CE	Yes
RoHS conform	Yes
References	
Accessories	10010070, 23510002, 23510003, 23510004, 23510005, 23510006, 23510007, 23510009, 39200000, 39200002

