



Product Features

Patchpanel with 12 universal modular jacks UM-Cat.6A iso 10G, shielded, for desktop-/wall mounting, DIN-rail mounting with DIN-rail mounting adapter 10010070, pure white (similar RAL 9010)

- quick mounting with latching lid
- fully shielded metal housing
- additional strain relief possibility for data cables with cable ties
- for desktop / wall mounting
- inscribable with marker 23510009
- performance universal modular jack:
 - Cat.6A iso universal module, shielded
 - for use in 10-Gigabit-Ethernet-Networks (transmission bandwidth 500 MHz)
 - 1 x RJ45 - opening
 - for standard keystone cutouts (14,8 x 19,3mm)
 - zinc diecast design
 - nickel-plated housing
 - 360° strain relief and shielding
 - suitable for Cat.6 and Cat.7 cable (Ø 6-10mm)
 - solid wires: IDC-terminals for one wire 0,51 - 0,64 mm Ø, AWG 24-22, maximum number of connections > 10-times
 - flexibel wires: IDC-terminals for one wire Leiter 0,13-0,22 mmØ AWG 26 (PE-Foamskin), AWG 24 (PE-solid)
 - 1 wire each contact, max. number of connections > 10-times
 - bend radius optimized cable entry (30°)
 - defined grounding via flat plug possible
 - mounting without any special tools
 - built-in dust protection (removeable)
 - colour code T568A and T568B according to EIA/TIA 568 A and B
 - suitable for PoE++ / 4PPOE according to IEEE 802.3bt
 - UPOE conform
 - HDBaseT conform
 - according to the following standards:
 - ISO/IEC 11801, Cat.6A, shielded
 - DIN EN 50173-1, Cat.6A, shielded
 - ANSI TIA/EIA-568-C.2 Category 6A
 - DIN IEC 60603-7-51, 500 MHz, shielded,
 - life > 750 cycles
 - RJ11/12-protected against mismatching
 - GHMT certified

Features	
General	
Surface	painted, high-gloss
Labeling field	Yes
shielded	Yes
Classification	Cat.6A iso
PoweroverEthernet	Yes
Protection class IP	20
Halogen Free	Yes
Statistical goods number	85369010
Country of manufacture	DE
GTIN (EAN)	4043921666623
Mounting types	
desktop design	Yes
DIN-Rail	Yes
surface-mounted	Yes
wall installation	Yes
Certifications	
GHMT	Yes
CE	Yes
RoHS conform	Yes
References	
Accessories	10010070, 23510002, 23510003, 23510004, 23510005, 23510006, 23510007, 39200002, 39200003

