



Abbildung ähnlich

**Product Features**

- |   |
|---|
| Basic-line splice box, extensible, 19"/1HE, 24xSC-D, OS2, APC, green                |
| - sheet steel housing, powder coated  |
| - labelled ports  |
| - with slide-in unit  |
| - can be tilted downwards when opened   |
| - front quick release (push-pull)   |
| - 4 splice cassettes for holding 12 or 24 pigtails                                  |
| - inserted crimp splice holder  |
| - prepared with pigtails inserted in bundle of 12 incl. 22 x SC-D ceramic couplings |
| - 48 SC-fibre pigtails E9/125 µm, 2 m, SM PC, grade C                               |
| - with test protocol for all fibres incl. serial number                             |
| - 2 x PG13.5/M20 - cable glands in the back (each 2 x right/left)                   |
| - 1 x PG13.5 gland in scope of delivery   |
| - black (similar to RAL 9005)   |

**Features**

<b>General</b>	
Surface	steel sheet, powder-coated
Classification	OS2 APC (8€)
Protection class IP	20
Halogen Free	Yes
GTIN (EAN)	4043921667149
<b>Mounting types</b>	
(19-inch)-installation, 1 rack unit	Yes
<b>Dimensions/Weights without packaging</b>	
Length mm	482
Width mm	245
Height mm	44
<b>Certifications</b>	
RoHS conform	Yes
<b>References</b>	
Accessories	228040502, 228040602, 228040802, 228040902, 228060500, 228060600, 228060800, 228060900, 228070000, 228070100, 228070200, 228070312