



Abbildung ähnlich

Product Features

Basic-line splice box, extensible, 19"/1U, 24xLC-D, OM4, erika

- sheet steel housing, powder coated
- labelled ports
- with slide-in unit
- can be tilted downwards when opened
- front quick release (push-pull)
- 4 splice cassettes for holding 12 or 24 pigtails
- inserted crimp splice holder
- prepared with pigtails inserted in bundle of 12 incl. 22 x LC-D ceramic couplings
- 48 LC-fibre pigtails G50/125 µm, 2 m, MM PC, grade C
- with test protocol for all fibres incl. serial number
- 2 x PG13.5/M20 - cable glands in the back (each 2 x right/left)
- 1 x PG13.5 gland in scope of delivery
- black (similar to RAL 9005)

Features

General	
Surface	steel sheet, powder-coated
Classification	OM4
Protection class IP	20
Halogen Free	Yes
GTIN (EAN)	4043921666968
Mounting types	
(19-inch)-installation, 1 rack unit	Yes
Dimensions/Weights without packaging	
Length mm	482
Width mm	245
Height mm	44
Certifications	
RoHS conform	Yes
References	
Accessories	228040002, 228040102, 228040302, 228060000, 228060100, 228060300, 228070000, 228070100, 228070200, 228070312