



Product Features

Anchoring clamps, housing made of stainless-steel 1.4301, hot galvanized, clamping range 8,5 to 18 mm Ø, tensile strength up to 2,5 kN, e.g for hanging cables

- clamping range 8,5 mm to 18 mm diameter
- hook diameter: 26mm
- max. tensile strength 2,5 kN
- housing made of stainless-steel 1.4301
- clamping jaws and positioning clips made of fibreglass reinforced PA (black)

Features

General

Surface	stainless steel
Halogen Free	Yes
Country of manufacture	DE
GTIN (EAN)	4043921666401

Dimensions/Weights without packaging

Length mm	237
Width mm	60,78
Height mm	39,8
Net weight piece kg	0,362

Certifications

RoHS conform	Yes
--------------	-----