



Product Features

PoE+ patch panel, midspan solution, surface mounting, for 6 PoE+ products, for desktop-/wall mounting, mounting on a DIN-rail with DIN-rail mounting adapter 10010070, 12 RJ45 ports, pure white (similar RAL 9010)

- for use in Gigabit- Ethernet- Networks
- DIN rail mounting with additional adapter
- fully shielded metal housing
- port assignment by colored dust caps
- inscribable with complementary marker
- suitable for PoE+ according to IEEE 802.3at
- for data rates up to 100Mbit/s
- life > 750 cycles (without PoE)
- additional power supply(ies) required

Features

General	
Surface	painted, high-gloss
Labeling field	Yes
shielded	Yes
PoweroverEthernet	Yes
Protection class IP	20
Halogen Free	Yes
Country of manufacture	DE
GTIN (EAN)	4043921666838
Mounting types	
desktop design	Yes
DIN-Rail	Yes
surface-mounted	Yes
wall installation	Yes
Dimensions/Weights without packaging	
Length mm	98
Width mm	238,5
Height mm	30,46
Certifications	
WEEE	Yes
CE	Yes
RoHS conform	Yes
References	
Accessories	10010070, 23510009, 23510306

