



# Verbatim Portable Monitors

January 2023

---

# Portable monitors overview

Model	Portable Display 14"	Portable Display 14" / 15.6" / 17.3" Touchscreen
Portable displays		
Panel Size	14"	14" / 15.6" / 17.3"
Panel	IPS LCD panel / LED-Backlight	
Resolution	1080p Full HD	
Touch Screen		Capacitive Touch Panel
Multi-touch		10 point touch screen
Touch Panel		G+FF technology
Aspect ratio	16:9	
View angles	H 178° / V 178° (Min)	
Input	- 2 x USB-C - 1 x standard HDMI (1.4) - 1 x USB-A 2.0	
Output	1 x Earphone Speaker 1W x 2(8Ω)	
Colours	16.7M colours	
Frame material	Plastic frame	Aluminium Alloy Frame
Supported technologies	Supports HDR / FreeSync / Low Blue Light	
Preset mode	Standard, TXT, Movie, Game, FPS, RTS	
Cables	1x Type-C (1.0M) 1x HDMI-HDMI (1.5M) 1x USB-A-Type-C (1.2M)	
Adapter	110V-240V 50/60HZ (Input)	

ETA: March 2023

## Portable Monitor 14" FULL HD 1080P

### PM-14

Reorder No: 49590

- Portable 14" monitor with Full HD resolution of 1920 x 1080 and 16.7M colours
- IPS Panel incl. full viewing angle of 178° and 16:9 screen ratio
- HDR technology improves picture quality creating a fantastic viewing experience
- Great compatibility for work/traveling/gaming: Connect the portable monitor to your PC/Mac/Tablet/Phones/Consoles with USB-C or HDMI
- One Cable Solution: Plug and play setup of compatible devices via USB-C connection
- Ultra Slim and Light Weight Design with integrated speaker
- Audio jack to connect headphones or speaker
- Multi-lingual user menu: English, French, Spanish, Italian and Russian
- Neoprene protective sleeve included
- Cables incl.: 1 x USB-C to USB-C, 1 x USB-A to USB-C, 1 x HDMI to HDMI, 1 x power adapter with EU and UK plug (for optional additional power supply)

Size: 14 inch

Contrast (typical): 1000:1

Resolution (H x V): 1920 x 1080

Aspect ratio: 16:9

View angles LR,UD (CR>10): H / V 178° (Min)

Display colours: 16.7M colours

Supports: HDR, FreeSync

Energy efficiency class: A

Input 1: USB-C x 2 (Full-featured USB-C)

Input 2: Standard HDMI (1.4) x 1

Output: USB-A 2.0 x 1

Dimensions (WxHxD):

328.92mm (W) x 209.05mm (H) x 6/12mm (D)

Net weight: 760g

Frame material: Plastic



# Portable Monitor 14" Full HD 1080P



Connection

Side view

Pack content

ETA: March 2023

## Portable Touchscreen Monitor Full HD 1080P Metal Housing

**PMT-14 14" / PMT-15 15.6" / PMT-17 17.3"**

Reorder No: 49591 / 49592 / 49593

- Portable Touchscreen Monitor with Full HD resolution of 1920 x 1080 and 16.7M colours in sizes: 14", 15.6" and 17.3"
- Supports capacitive 10-point multi-touch with G+FF technology; simply connect the monitor to your device using a USB-C cable
- IPS Panel incl. full viewing angle of 178° and 16:9 screen ratio
- Solid and durable aluminium housing
- HDR technology improves picture quality creating a fantastic viewing experience
- Great compatibility for work/traveling/gaming: Connect the portable monitor to your PC/Mac/Tablet/Phones/Consoles with USB-C or HDMI.
- One Cable Solution: Plug and play setup of compatible devices via USB-C connection
- Ultra Slim and Light Weight Design with integrated speaker.
- Audio jack to connect headphones or speaker
- Neoprene protective sleeve included
- Cables incl.: 1 x USB-C to USB-C, 1 x USB-A to USB-C, 1 x HDMI to HDMI, 1 x power adapter with EU and UK plug (for optional additional power supply)

Size: 14 / 15.6 / 17.3 inch

Touchscreen: Capacitive touch panel

Multi-touch: 10 points

Contrast (typical): 1000:1

Resolution (H x V): 1920 x 1080

Aspect ratio: 16:9

View angles LR,UD (CR>10): H / V 178° (Min)

Display colours: 16.7M colours

Supports: HDR, FreeSync

Input 1: USB-C x 2 (Full-featured USB-C)

Input 2: Standard HDMI (1.4) x 1

Output: USB-A 2.0 x 1

Frame material: Aluminium

Energy efficiency class: A



# Portable Touchscreen Monitor Full HD Metal Housing



Connection



Side view



Pack content

Thank you

---