

Artikel Nr.: 975344




Fliesen-Profil Ecke innen EV-01-08 passend für 8 - 9,3 mm LED Stripes

Charakteristik

Material	Aluminium
Farbe	Silber-matt
Optik	eloxiert
	0,00

Abmessungen und Gewicht

Länge	3000,00
Breite	43,00
Höhe	43,00
Durchmesser	0,00
Gewicht	1245 g

Montage**Befestigungsmöglichkeiten**

- für eine optimale Montage empfehlen wir einen flexiblen Fliesenkleber und Flexfugenmörtel zu verwenden
- eine optimale Arbeitsgrundlage sollte staubfrei und mit einem für die Oberfläche passenden Haftgrund vorbehandelt werden. Somit erzielen Sie optimale und dauerhafte Ergebnisse
- zur Montage der Profile empfehlen wir Fliesen oder Feinsteinzeug
- der Auftrag des flexiblen Fliesenklebers sollte durch eine 6 x 6mm oder 8 x 8mm Zahntraufel vorgenommen werden

Artikel Nr.: 975344

tiles-profile inner corner EV-01-08 suitable for 8 - 9,3 mm LED Stripes




Characteristics

Material	aluminum
Color	matt silver
Optic	anodized

Dimensions & Weight

Length	3000,00
Width	43,00
Height	43,00
Diameter	0,00
Product Weight	1245 g

Mounting



Mounting Options

- we recommend a flexible tile adhesive and joint grout
- working basis should be treated free from dust and to be treated with surface matching bonding primer for an optimal and long lasting result
- for mounting the profile we recommend tiles or porcelain stoneware
- for application of flexible tile adhesive use a 6 x 6mm or 8 x 8mm notched trowel