

Artikel Nr.: 348087

Deckenaufbauleuchte, Indi III, silberfarben, 220-240V AC/50-60Hz, 3x max. 50,00 W

Technische Daten

Charakteristik

Material	Aluminium / Aluminium
Farbe	silberfarben / Silber
Optik	gebürstet/ Chrom
im Lieferumfang	2x Schrauben mit Dübel, 1x Saugheber



Elektrische Daten

Leistung	3x max. 50,00 W
Eingangsspannung	220-240V AC/50-60Hz
Eingangsstrom	
Fassung / Sockel	GU10
Anzahl Sockel	3
Netzgerät	
Ansteuerung	dimmbar über optionales Leuchtmittel
Anschlussmöglichkeit	Klemme
Schutzklasse I, II, III	I




Artikel Nr.: 348087

Deckenaufbauleuchte, Indi III, silberfarben, 220-240V AC/50-60Hz, 3x max. 50,00 W

Lichtrichtung

Dreh- und Schwenkbereich	dreh-schwenkbar
Neigungswinkel	90°
Abstrahlverhalten	
Reflektor / Linse	



Abmessungen und Gewicht

Länge	0,00
Breite	0,00
Höhe	124,00
Durchmesser	250,00
Deckenabhängung	0,00
Gewicht	764 g

Sockelmaß

Länge	0,00
Breite	0,00
Höhe	25,00
Durchmesser	190,00

Artikel Nr.: 348087

Deckenaufbauleuchte, Indi III, silberfarben, 220-240V AC/50-60Hz, 3x max. 50,00 W

Grenzwerte

Betriebstemperatur	-5°C - +40°C
Lagertemperatur	-10°C - +40°C
IP - Schutzart	IP20

EEI	Die Leuchte ist geeignet für Leuchtmittel der Energieeffizienzklassen A++ bis E
IP20	Schutz gegen das Eindringen von Fremdkörper > 50 mm. Kein Schutz gegen das Eindringen von Wasser.
	Leuchte der Schutzklasse I bei der der Schutz gegen elektrischen Schlag nicht allein auf der Basisisolierung beruht, sondern die eine zusätzliche Sicherheitsvorkehrung derart enthält, dass berührbare leitfähige Teile mit Mitteln zum Anschluss an den Schutzleiter der festen Installation ausgerüstet sind, so dass im Fehlerfall der Basisisolierung berührbare leitfähige Teile nicht aktiv werden können.

Article no.: 348087

Surface mounted ceiling lamp, Indi III, silver, 220-240V AC/50-60Hz, 3x max. 50,00 W

Technical Data

General Characteristics

Material	aluminum / aluminum
Colour	silver / silver
Optics	brushed / chrome
included in delivery	2x screws with dowels, 1x vacuum lifting pad



Electrical Characteristics


Power	3x max. 50,00 W
Input voltage	220-240V AC/50-60Hz
Input current	
Base (standard designation)	GU10
Number of bases	3
Power supply unit	
Electronically reversible	dimnable via optional bulb
Connection possibility	clamp
Protection class I, II, III	I

Article no.: 348087

Surface mounted ceiling lamp, Indi III, silver, 220-240V AC/50-60Hz, 3x max. 50,00 W

Light Direction

Rotating and tilting range	rotatable-swivel
Angle of inclination	90°
Radiation direction	
Reflector / lense	



Dimensions & Weight

Length	0,00
Width	0,00
Height	124,00
Diameter	250,00
Suspensions from ceiling	0,00
Product Weight	764 g

Base dimensions

Length	0,00
Width	0,00
Height	25,00
Diameter	190,00

Article no.: 348087

Surface mounted ceiling lamp, Indi III, silver, 220-240V AC/50-60Hz, 3x max. 50,00 W

Absolute maximum ratings

Working temperature	-5°C - +40°C
Storage temperature	-10°C - +40°C
IP - Code	IP20

EEI	The luminaire is suitable for lamps of energy efficiency classes A++ to E.
IP20	Protection against penetration of foreign objects > 50 mm. No protection against penetration of water.
	Lightings of Protection Class I in which the protection against electric shock is not based solely on isolation, but an additional safety measure contains such a way that accessible conductive parts are equipped with means for connection to the protective conductor of the fixed installation, so that in case of failure of the basic insulation exposed conductive parts cannot be active.