



**Artikel Nr.: 342103**

Pendelleuchte, Pavonis, Grau, 220-240V AC/50-60Hz, 1x max. 25,00 W



**Technische Daten**

**Charakteristik**

<b>Material</b>	Beton
<b>Farbe</b>	Grau
<b>Optik</b>	überstreichbar
<b>im Lieferumfang</b>	

**Elektrische Daten**

<b>Leistung</b>	1x max. 25,00 W
<b>Eingangsspannung</b>	220-240V AC/50-60Hz
<b>Eingangsstrom</b>	
<b>Fassung / Sockel</b>	E27
<b>Anzahl Sockel</b>	1
<b>Netzgerät</b>	
<b>Ansteuerung</b>	dimmbar über optionales Leuchtmittel
<b>Anschlussmöglichkeit</b>	Klemme
<b>Schutzklasse I, II, III</b>	I



**Artikel Nr.: 342103**

Pendelleuchte, Pavonis, Grau, 220-240V AC/50-60Hz, 1x max. 25,00 W



**Lichtrichtung**


Dreh- und Schwenkbereich	
Neigungswinkel	
Abstrahlverhalten	
Reflektor / Linse	

**Abmessungen und Gewicht**

Länge	
Breite	
Höhe	199 mm
Durchmesser	140 mm
Deckenabhängung	1,50 m
Gewicht	2000 g

**Sockelmaß**

Länge	
Breite	
Höhe	25 mm
Durchmesser	100 mm





**Artikel Nr.: 342103**

Pendelleuchte, Pavonis, Grau, 220-240V AC/50-60Hz, 1x max. 25,00 W



**Grenzwerte**

Betriebstemperatur	-5°C - +40°C
Lagertemperatur	-10°C - +60°C
IP - Schutzart	IP 20

**EEl** Die Leuchte ist geeignet für Leuchtmittel der Energieeffizienzklassen A++ bis E

**IP 20** Schutz gegen das Eindringen von Fremdkörper > 50 mm. Kein Schutz gegen das Eindringen von Wasser.



Leuchte der Schutzklasse I bei der der Schutz gegen elektrischen Schlag nicht allein auf der Basisisolierung beruht, sondern die eine zusätzliche Sicherheitsvorkehrung derart enthält, dass berührbare leitfähige Teile mit Mitteln zum Anschluss an den Schutzleiter der festen Installation ausgerüstet sind, so dass im Fehlerfall der Basisisolierung berührbare leitfähige Teile nicht aktiv werden können.



**Article no.: 342103**

Pendant lamp, Pavonis, gray, 220-240V AC/50-60Hz, 1x max. 25,00 W



**Technical Data**

**General Characteristics**

<b>Material</b>	concrete
<b>Colour</b>	gray
<b>Optics</b>	paintable
<b>included in delivery</b>	

**Electrical Characteristics**

<b>Power</b>	1x max. 25,00 W
<b>Input voltage</b>	220-240V AC/50-60Hz
<b>Input current</b>	
<b>Base (standard designation)</b>	E27
<b>Number of bases</b>	1
<b>Power supply unit</b>	
<b>Electronically reversible</b>	dimnable via optional bulb
<b>Connection possibility</b>	clamp
<b>Protection class I, II, III</b>	I



**Article no.: 342103**

Pendant lamp, Pavonis, gray, 220-240V AC/50-60Hz, 1x max. 25,00 W



**Light Direction**


Rotating and tilting range	
Angle of inclination	
Radiation direction	
Reflector / lense	

**Dimensions & Weight**

Length	
Width	
Height	199 mm
Diameter	140 mm
Suspensions from ceiling	1,50 m
Product Weight	2000 g

**Base dimensions**

Length	
Width	
Height	25 mm
Diameter	100 mm





**Article no.: 342103**

Pendant lamp, Pavonis, gray, 220-240V AC/50-60Hz, 1x max. 25,00 W



**Absolute maximum ratings**

Working temperature	-5°C - +40°C
Storage temperature	-10°C - +60°C
IP - Code	IP 20

---

**EEl** The luminaire is suitable for lamps of energy efficiency classes A++ to E.

---

**IP 20** Protection against penetration of foreign objects > 50 mm. No protection against penetration of water.



Lightings of Protection Class I in which the protection against electric shock is not based solely on isolation, but an additional safety measure contains such a way that accessible conductive parts are equipped with means for connection to the protective conductor of the fixed installation, so that in case of failure of the basic insulation exposed conductive parts cannot be active.