

Artikel Nr.: 733064

Energieverteiler, Facado Socket, Dunkelgrau, 220-240V AC/50-60Hz, 1x max. 20,00 W

Technische Daten

Charakteristik

Material	Aluminium Druckguss
Farbe	Dunkelgrau
Optik	
im Lieferumfang	



Elektrische Daten

Leistung	1x max. 20,00 W
max. Anschlussleistung	3680 W
Eingangsspannung	220-240V AC/50-60Hz
Eingangsstrom	
Fassung / Socket	E27
Anzahl Socket	1
Netzgerät	
Anschlussmöglichkeit	Klemme
Schutzklasse I, II, III	I



Artikel Nr.: 733064


Energieverteiler, Facado Socket, Dunkelgrau, 220-240V AC/50-60Hz, 1x max. 20,00 W

Lichtrichtung

Dreh- und Schwenkbereich	feststehend
Neigungswinkel	
Abstrahlverhalten	
Reflektor / Linse	symmetrisch

Abmessungen und Gewicht

Länge	650,00
Breite	108,00
Höhe	108,00
Durchmesser	0,00
Gewicht	3024 g



Grenzwerte

Betriebstemperatur	-20°C - +45°C
Lagertemperatur	-20°C - +60°C
IP - Schutzart	IP54

IP54 Schutz gegen das Eindringen von Staub. (Staubschutz) Geschützt gegen Spritzwasser.



Leuchte der Schutzklasse I bei der der Schutz gegen elektrischen Schlag nicht allein auf der Basisisolierung beruht, sondern die eine zusätzliche Sicherheitsvorkehrung derart enthält, dass berührbare leitfähige Teile mit Mitteln zum Anschluss an den Schutzleiter der festen Installation ausgerüstet sind, so dass im Fehlerfall der Basisisolierung berührbare leitfähige Teile nicht aktiv werden können.



Aufgrund des komplexen Herstellungsprozesses von LED stellen die angegebenen Werte nur rein statistische Größen dar und müssen nicht zwingend den tatsächlichen Parametern jedes einzelnen LED-Moduls entsprechen, sondern können von den typischen Werten abweichen.

Article no.: 733064

Energy distributor, Facado Socket, dark gray, 220-240V AC/50-60Hz, 1x max. 20,00 W

Technical Data**General Characteristics**

Material	aluminum die casting
Colour	dark gray
Optics	
included in delivery	

**Electrical Characteristics**

Power	1x max. 20,00 W
max. Connection Power	3680 W
Input Voltage	220-240V AC/50-60Hz
Input current	
Base (standard designation)	E27
Number of Bases	1
Power supply unit	
Connection possibility	clamp
Protection class I, II, III	I



Article no.: 733064


Energy distributor, Facado Socket, dark gray, 220-240V AC/50-60Hz, 1x max. 20,00 W

Light Direction

Rotating and tilting range	fixed
Angle of inclination	
Radiation direction	
Reflector / lense	symmetrisch

Dimensions & Weight

Length	650,00
Width	108,00
Height	108,00
Diameter	0,00
Product Weight	3024 g



Absolute maximum ratings

Working temperature	-20°C - +45°C
Storage temperature	-20°C - +60°C
IP - Code	IP54

IP54 Protection against penetration of dust. (dust protected) Protection against penetration of splashing water.



Lightings of Protection Class I in which the protection against electric shock is not based solely on isolation, but an additional safety measure contains such a way that accessible conductive parts are equipped with means for connection to the protective conductor of the fixed installation, so that in case of failure of the basic insulation exposed conductive parts cannot be active.



Because of the complex manufacturing process of the LED the above shown data are just a statistical size, which is not forced to be the realistic data of every LED.