

Artikel Nr.: 730408

Deckenaufbauleuchte, Mob Round I, anthrazit, 220-240V AC/50-60Hz, 1x max. 9,00 W

Technische Daten

Charakteristik

Material	Aluminium Druckguss
Farbe	anthrazit
Optik	
im Lieferumfang	



Elektrische Daten

Leistung	1x max. 9,00 W
Eingangsspannung	220-240V AC/50-60Hz
Eingangsstrom	
Fassung / Sockel	GX53
Anzahl Sockel	1
Netzgerät	
Ansteuerung	dimmbar über optionales Leuchtmittel
Anschlussmöglichkeit	Klemme
Schutzklasse I, II, III	I



Artikel Nr.: 730408

Deckenaufbauleuchte, Mob Round I, anthrazit, 220-240V AC/50-60Hz, 1x max. 9,00 W

Lichttrichtung


Dreh- und Schwenkbereich	feststehend
Neigungswinkel	
Abstrahlverhalten	
Reflektor / Linse	

Abmessungen und Gewicht

Länge	
Breite	
Höhe	92 mm
Durchmesser	108 mm
Deckenabhängung	
Gewicht	641 g

Sockelmaß

Länge	
Breite	
Höhe	
Durchmesser	100 mm



Artikel Nr.: 730408

Deckenaufbauleuchte, Mob Round I, anthrazit, 220-240V AC/50-60Hz, 1x max. 9,00 W

Grenzwerte

Betriebstemperatur	-20°C - +40°C
Lagertemperatur	-10°C - +60°C
IP - Schutzart	IP54

EEI	Die Leuchte ist geeignet für Leuchtmittel der Energieeffizienzklassen A++ bis E
IP54	Schutz gegen das Eindringen von Staub. (Staubschutz) Geschützt gegen Spritzwasser.
	Leuchte der Schutzklasse I bei der der Schutz gegen elektrischen Schlag nicht allein auf der Basisisolierung beruht, sondern die eine zusätzliche Sicherheitsvorkehrung derart enthält, dass berührbare leitfähige Teile mit Mitteln zum Anschluss an den Schutzleiter der festen Installation ausgerüstet sind, so dass im Fehlerfall der Basisisolierung berührbare leitfähige Teile nicht aktiv werden können.

Article no.: 730408

Surface mounted ceiling lamp, Mob Round I, anthracite, 220-240V AC/50-60Hz, 1x max. 9,00 W

Technical Data

General Characteristics

Material	aluminum die casting
Colour	anthracite
Optics	
included in delivery	



Electrical Characteristics

Power	1x max. 9,00 W
Input voltage	220-240V AC/50-60Hz
Input current	
Base (standard designation)	GX53
Number of bases	1
Power supply unit	
Electronically reversible	dimnable via optional bulb
Connection possibility	clamp
Protection class I, II, III	I



Article no.: 730408

Surface mounted ceiling lamp, Mob Round I, anthracite, 220-240V AC/50-60Hz, 1x max. 9,00 W

Light Direction


Rotating and tilting range	fixed
Angle of inclination	
Radiation direction	
Reflector / lense	

Dimensions & Weight

Length	
Width	
Height	92 mm
Diameter	108 mm
Suspensions from ceiling	
Product Weight	641 g

Base dimensions

Length	
Width	
Height	
Diameter	100 mm



Article no.: 730408

Surface mounted ceiling lamp, Mob Round I, anthracite, 220-240V AC/50-60Hz, 1x max. 9,00 W

Absolute maximum ratings

Working temperature	-20°C - +40°C
Storage temperature	-10°C - +60°C
IP - Code	IP54

EEI	The luminaire is suitable for lamps of energy efficiency classes A++ to E.
IP54	Protection against penetration of dust. (dust protected) Protection against penetration of splashing water.
	Lightings of Protection Class I in which the protection against electric shock is not based solely on isolation, but an additional safety measure contains such a way that accessible conductive parts are equipped with means for connection to the protective conductor of the fixed installation, so that in case of failure of the basic insulation exposed conductive parts cannot be active.