

ThinkVision LT2423 60A8KAT2EU

Product

ThinkVision LT2423

Region

EMEA

Color

Black

Panel

Twisted Nematic

Display Size

24"

View Area

531.4x298.9 mm

Resolution

1920x1080

Aspect Ratio

16:9

Pixel Pitch

0.27x0.27 mm

Dot / Pixel Per Inch

92 dpi

Brightness

250 nits

Contrast Ratio

1000:1

Pixel Response Time

5 ms

Color Gamut

72%

View Angle (H / V)

170 / 160

Stand

Tilt Stand

Side Bezel Width

17 mm

Dimensions with Stand (HxWxD)

414.3x567.1x216.7 mm

Power Consumption (Typical / Maximum)

21W / 31W

Power Adapter

Integrated

Weight (Including Stand)

8.30lb / 3.76kg

Warranty

3-year

ENERGY STAR

ENERGY STAR 6.0

TCO

TCO 6.0

EPEAT

Gold

Presets / User Settings

24 / 20

On Screen Display

OSD, 8 Languages

USB Port

None

Speaker

Stereo 3Wx2

Camera

None

Multiple Input

VGA, HDMI

Monitor Cable

VGA

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Operating System

Support Windows 8

Ann Date (mm/yy)

07/13

WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.




<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2023. All rights reserved.



Lenovo™

<p>Name LT2423 Wide Flat Panel Monitor Case color Business black Type-model 60A8KAR2US / 60A8KAT2EU Panel TFT-LCD, twisted nematic (TN), White LED backlight Viewable image size 24" (610mm) diagonal Max view area (W x H) 20.9" x 11.8" (531.4mm x 298.9mm) Optimum resolution 1920x1080 Max pixel rate 205MHz Aspect ratio 16:9 Pixel pitch (mm) 0.278mm Dot/Pixel per Inch 92 dpi Brightness 250 nits or cd/m² (typical) Contrast ratio 1000:1 (typical) Contrast ratio 2000000:1 Pixel response time 5ms Color gamut 72% Viewing angle at 10:1 CR 170° horizontal, 160° vertical Stand Tilt stand Bezel width Sides: 0.67" (17.0mm); top: 0.67" (17.0mm); bottom: 1.02" (26.0mm)</p> <p>Dimensions (HxWxD, excluding stand) 13.53" H x 22.33" W x 1.97" D; Dimensions (HxWxD, including stand) 343.7mm H x 567.1mm W x 50.0mm D Dimensions (HxWxD, including stand) 16.30" H x 22.33" W x 8.50" D; Dimensions (HxWxD, including stand) 414.3mm H x 567.1mm W x 216.7mm D Power supply 21 watts typical, 31 watts maximum, <0.5 watts standby/suspend, universal, integrated (no external brick-like power supply)</p> <p>Weight 8.30 lb; 3.76kg Limited warranty⁴ 3 year (includes backlight) Available date July 2013</p>	<p>Features</p> <ul style="list-style-type: none"> • Widescreen 24-inch monitor • Supports 1920x1080 resolution • Two 3W stereo speakers • Audio in (3.5mm) • Supports VGA and HDMI 1.4 interfaces • Supports optional soundbar • Support Lenovo Tiny PC and 3rd party thin client via optional Lenovo bracket • Microsoft® Windows® 8 certified • Arsenic/Lead/Mercury free 																
<p>VESA-compliant² VESA DDC2B/CI Power management ENERGY STAR® 6.0 Ergonomics ISO 9241-307 Emission standards MPR-2, FCC Class B Environmental TCO Displays 6.0, TCO Certified Edge 1.2, WEEE, RoHS, EPEAT™ Gold rating, ULE Gold</p> <p>Preset resolutions</p> <table border="0"> <tr> <td>VGA:</td> <td>640x350, 640x480, 720x400</td> </tr> <tr> <td>SVGA:</td> <td>800x600, 832x624</td> </tr> <tr> <td>XGA:</td> <td>1024x768, 1152x864</td> </tr> <tr> <td>SXGA:</td> <td>1280x1024</td> </tr> <tr> <td>WXGA:</td> <td>1366x768</td> </tr> <tr> <td>WXGA+:</td> <td>1440x900, 1600x900</td> </tr> <tr> <td>WSXGA+:</td> <td>1680x1050</td> </tr> <tr> <td>Full HD:</td> <td>1920x1080</td> </tr> </table> <p>Presets / user settings Standard presets: 24; User settings: 20</p>	VGA:	640x350, 640x480, 720x400	SVGA:	800x600, 832x624	XGA:	1024x768, 1152x864	SXGA:	1280x1024	WXGA:	1366x768	WXGA+:	1440x900, 1600x900	WSXGA+:	1680x1050	Full HD:	1920x1080	 <p>ThinkVision LT2423 Wide Monitor</p>
VGA:	640x350, 640x480, 720x400																
SVGA:	800x600, 832x624																
XGA:	1024x768, 1152x864																
SXGA:	1280x1024																
WXGA:	1366x768																
WXGA+:	1440x900, 1600x900																
WSXGA+:	1680x1050																
Full HD:	1920x1080																
<p>Viewing adjustments Tilt: 22° back, -5° forward Rotating screen None On screen display On screen display with digital user controls (8 languages) Control features Direct access (buttons on front) for automatic image setup, input switch, and brightness Multimedia Integrated stereo speakers (3 watts x 2) Multiple input Dual input (two different PCs attach to two different connectors; one PC shows image; select via button) Monitor connectors (1) VGA 15-pin D-shell, analog, blue (2) HDMI (1.4), digital, HDCP-compliant Signal cables (1) detachable, VGA 15-pin D-shell at each end, analog, 1.8 meter Mounting features Wall or desk mounting using the Extend Arm or third-party accessories meeting the VESA FPMPI® (100mm mount) Security Security keyhole for attachment of optional cable lock (Kensington® lock-compatible)</p>																	
<p>Ship group Monitor, attached stand, Setup poster, Safety and Warranty Information, 1.8 meter analog signal cable, 1.8 meter Audio cable, 1.8 meter black power cord</p>																	
<p>Limited Warranty</p> <p>See details at http://support.lenovo.com/en_US/guides-and-manuals/detail.page?DocID=UM008281</p>	<p>Accessories</p> <table border="0"> <tr> <td>Kensington MicroSaver Cable Lock</td> <td>73P2582</td> </tr> <tr> <td>Kensington Twin Head Cable Lock</td> <td>45K1620</td> </tr> <tr> <td>Lenovo Security Cable Lock</td> <td>57Y4303</td> </tr> <tr> <td>ThinkCentre Extend Arm</td> <td>57Y4352</td> </tr> <tr> <td>Lenovo Easy Reach Monitor Stand</td> <td>55Y9258</td> </tr> </table> <p>See details at www.lenovo.com/support/monitoraccessories</p> <p>See all monitors at www.lenovo.com/thinkvision</p>	Kensington MicroSaver Cable Lock	73P2582	Kensington Twin Head Cable Lock	45K1620	Lenovo Security Cable Lock	57Y4303	ThinkCentre Extend Arm	57Y4352	Lenovo Easy Reach Monitor Stand	55Y9258						
Kensington MicroSaver Cable Lock	73P2582																
Kensington Twin Head Cable Lock	45K1620																
Lenovo Security Cable Lock	57Y4303																
ThinkCentre Extend Arm	57Y4352																
Lenovo Easy Reach Monitor Stand	55Y9258																

ThinkVision LT2423



Lenovo™