

Balcony power plant bracket Pro 300W TX-227

Universal bracket for solar panels



- Easy assembly
- Made in Germany
- DGS certified
- Statically tested bracket
- 3 mounting options (balcony (round+square), free-standing, wall mounting)
- 3 adjustable mounting angle (30°, 35°, 40°)
- High quality 6mm aluminum profile

Technical Specifications:

- Max. snow load: 158kg/m² (snow zone 2, Germany)
- Max. wind force: 25m/s (wind zone 2; Germany)
- Material: Aluminum (EN AW-6060)

Dimensions:

- Alu-profile (long) (LxWxH): 105 x 6 x 4cm (6mm)
- Alu-profile (short) (LxWxH): 95 x 6 x 4cm (6mm)
- Alu-profile (angle) (LxWxH): 51 x 4 x 4cm (4mm)
- Alu-U-profile (LxWxH): 12 x 6 x 6cm (5mm)
- Built up (LxWxH): 95 x 6 x 51cm
- Weight: 8.2kg

Compatibility:

TX-213, TX-212 or Module hole distance: 91.5-100cm

Package Contents:

2x Alu-profile (long), 2x Alu-profile (short), 2x Alu-profile (angle), 4x Alu-U-profile, 4x Spacer washer (60x120x5mm), 20x Hex nut M8, 4x Rubber strip (2mm 120x140mm), 4x Pan head screws M8 x20, 8x Wing nut M8

Article No.: 5039

