



# LogiLink®

## USB-C™ GaN 40 W Dual Ports Wall Charger

Art. No.: PA0282



# Compact & More Powerful

GaN chargers are physically smaller, and conduct higher voltages than silicon-based chargers with better heat dissipation. Charge two smartphones, tablets or laptop at full speed with 40 W USB-C Power Delivery at home, in the office, or on-the-go.



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.


**GaN Chargers** are smaller since they require much fewer components compared to silicon chargers.

**Smaller  
& Lighter**



They also work more efficiently at much higher voltages than silicon chargers.

**3x  
Faster**



Up to 40 W output for a variety of devices from tablets to smartphones; it powers your devices at incredible speeds.

**20W+20W**

**Fast Charging** 

**PPS** 

Supports PPS (Programmable Power Supply) charging and adjusting the output power in real-time, depending on device's charging status, feeding it with maximum power.



Extremely safe as it comes with overcurrent, overvoltage, overheating and short circuit protections.



Compact size makes it lightweight and easily fits into your laptop bag or backpack. The perfect mobile accessory for traveling.



Widely compatible with most USB-C devices such as smartphones, tablets and much more.



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.



PA0282



Made in China

## Specification:

Input	230 V AC 50/60 Hz 1 A
Output	USB-C 1: 5 V/3 A (15 W), 9 V/2,22 A (19,98 W), 12 V/1,67 A (20 W) USB-C 2: 5 V/3 A (15 W), 9 V/2,22 A (19,98 W), 12 V/1,67 A (20 W) PPS: 3,3–11 V/1,8 A Max. total output: 40 W
Efficiency	Level VI
LED Indication	Yes
Operating Temperature	-10–40 °C
Storage Temperature	-20–80 °C
Relative Humidity	35–85% (non-condensing)
Storage Humidity	5–95% (non-condensing)
Color	White
Dimensions	5,5 x 3,25 x 5,43 cm (without plug) 5,5 x 3,586 x 9,25 cm (with plug)
Weight	105 g



## Package Contents:

- » 1x USB-C Wall Charger
- » 1x User Manual

## Package Information:

- » Packing Dimension: 120 x 75 x 40 mm
- » Packing Weight: 0,14 kg
- » Carton Dimension: 420 x 320 x 140 mm
- » Carton Q'ty: 40 pcs
- » Carton Weight: 5,6 kg



! Proper use of the PD function can only be guaranteed in combination with certified USB cables with E-Mark chipset.

\*The specifications and pictures are subject to change without prior notice.

\*All trade names referenced are the registered trademarks of their respective owners.



PA0282



Made in China