



TECHNICAL DATA

Item no.	1006425
Socket	GU10
Lamp	LED GU10 51mm
Number of sockets	2
Lamps included	No
Tilt range	90 °
Horizontal rotation range	350 °
IP Code	IP 20
Assembly	Surface
Assembly details	Ceiling,Wall
Primary nominal voltage	220-240V ~50/60Hz
Safety class	I
Wattage	10 W
Ambient temperature	25 °C
Color	black
Length	12.5 cm
Height	13 cm
Diameter	7 cm
Net weight	0.817 kg
Gross weight	0.874 kg