



TECHNICAL DATA

Item no.	1006424
Socket	GU10
Lamp	LED GU10 51mm
Number of sockets	1
Lamps included	No
Tilt range	90 °
Horizontal rotation range	350 °
IP Code	IP 20
Assembly	Surface
Assembly details	Ceiling,Wall
Primary nominal voltage	220-240V ~50/60Hz
Safety class	I
Wattage	10 W
Ambient temperature	25 °C
Color	white
Length	12.5 cm
Height	13 cm
Diameter	7 cm
Net weight	0.428 kg
Gross weight	0.458 kg

Recommended lamp

1005076	LED lightbulb QPAR51 , GU10, 2700K, white
1005079	LED lightbulb QPAR51 , GU10, 3000K, white
1005082	LED lightbulb QPAR51 , GU10, 4000K, white
1005273	QPAR51 GU10 , LED light, 6W 2200 2700K CRI90 36°

Accessories

1006449	
1006450	
1006451	
1007190	